



80Vmax (40Vmax X2) Brushless Breaker XGT®

HM004G

40Vmax X2, HEX 28.6 mm, 72.8 J

Model HM004G is an 80Vmax cordless breaker powered by two 40Vmax XGT® Li-Ion batteries in series. With 80Vmax high voltage and a Brushless motor, this cordless model has achieved power similar to the existing corded models.

The main features and benefits are: Low Vibration (Anti-Vibration Technology), Maintenance warning function, Equipped with AWS (Auto-start Wireless System).



Technical specifications

Nominal Battery Voltage	2 x 40 V
Voltage XGT	✓
Brushless Motor	✓
Battery Chemistry (Ni-Cd / Ni-MH / Li-ion)	Li-ion
Impacts per Minute (IPM)	870 min ⁻¹
Impact Energy	72,8 J
AWS ready	✓
Sound Power Level (L _{WA})	103 dB(A)
Sound Pressure Level (L _{pA})	95 dB(A)
Noise Uncertainty (K Factor)	1,6 dB(A)
Tool weight with battery	29,7 - 32,1 kg
Product Dimensions (L x W x H):	882 x 227 x 540 mm
Vibration Level, Chiselling	6,5 m/s ²
Vibration Uncertainty (K Factor), Chiselling	1,5 m/s ²

User benefits

- Soft start suppresses start-up reaction for more control and better accuracy
- Auto-start Wireless System (AWS) connects to compatible vacuum cleaners with Bluetooth
- Twin LED lights with pre-glow and afterglow functions for better illumination and more accurate work
- AVT (Anti-Vibration Technology) ensures extra-low vibration performance
- Battery protection circuit protects against overloading, over-discharging and over-heating
- Constant speed control maintains constant speed under load

Link to product - www.makita.uk.com



Related products

Optional AC

B-10372

Bull Point Chisel, 28.6mm

D-29228

Scaling Chisel, 75 x 410 mm



D-17631

Bull point 410 mm, 28,6 mm Hex



P-05717

Spade chisel 125 x 400 mm



Other

User manual

Parts drawing