

42AS

combination wrenches, open and offset ring ends

• Inch sizes

	art.	"	L mm	A mm	Ø mm	S1 mm	S2 mm	g
000421106	42AS 1/4	1/4x1/4	95	15,2	10,1	3,4	5,2	12
000421107	42AS 9/32	9/32x9/32	106	17,1	11,1	3,6	5,7	18
000421108	42AS 5/16	5/16x5/16	116	19,0	12,3	3,9	6,2	23
000421110	42AS 3/8	3/8x3/8	137	22,8	15,1	4,5	7,1	35
000421111	42AS 7/16	7/16x7/16	148	24,8	16,5	4,8	7,5	44
000421113	42AS 1/2	1/2x1/2	169	28,8	19,6	5,4	8,4	66
000421114	42AS 9/16	9/16x9/16	180	30,8	21,0	5,7	8,8	80
000421115	42AS 19/32	19/32x19/32	191	32,7	22,4	6,0	9,2	95
000421116	42AS 5/8	5/8x5/8	201	34,6	23,8	6,3	9,7	105
000421117	42AS 11/16	11/16x11/16	212	36,6	25,2	6,7	10,2	120
000421119	42AS 3/4	3/4x3/4	233	40,5	28,0	7,3	11,4	160
000421121	42AS 13/16	13/16x13/16	254	44,5	30,7	7,9	12,4	205
000421122	42AS 7/8	7/8x7/8	264	46,4	32,2	8,1	12,8	225
000421124	42AS 15/16	15/16x15/16	285	50,3	34,9	8,5	13,5	290
000421125	42AS 1	1x1	296	52,3	36,2	8,7	13,8	310
000421127	42AS 1.1/16	1.1/16x1.1/16	317	56,2	39,0	9,1	14,6	375
000421129	42AS 1.1/8	1.1/8x1.1/8	338	60,2	41,9	9,5	15,3	450
000421132	42AS 1.1/4	1.1/4x1.1/4	370	66,0	45,7	10,1	16,2	565
000421133	42AS 1.5/16	1.5/16x1.5/16	391	70,0	48,5	10,5	16,8	680
000421135	42AS 1.3/8	1.3/8x1.3/8	412	73,9	51,3	10,7	17,5	835
000421136	42AS 1.7/16	1.7/16x1.7/16	412	73,9	51,3	10,9	17,5	825
000421138	42AS 1.1/2	1.1/2x1.1/2	433	77,9	54,0	11,3	18,2	965

