



## PRODUCT DEFINITION

|                                  |          |
|----------------------------------|----------|
| <b>Brand</b>                     | NTN      |
| <b>d - Internal diameter</b>     | 35 mm    |
| <b>D - External diameter</b>     | 68 mm    |
| <b>T - Thrust bearing height</b> | 24 mm    |
| <b>rs - Min fillet radius</b>    | 1 mm     |
| <b>Mass</b>                      | 0,383 kg |

## PRODUCT PERFORMANCE

|   |              |
|---|--------------|
| <b>Ca - Dynamic axial load rating</b>         | 55500000 mN  |
| <b>C0a - Static axial load rating</b>         | 105000000 mN |
| <b>Cua - Limit axial load rating</b>          | 4750000 mN   |
| <b>N lim - Oil lubrication limit speed</b>    | 21000 °/s    |
| <b>N lim - Grease lubrication limit speed</b> | 14400 °/s    |
| <b>Tmin - Min operating temperature</b>       | 233,15 °K    |
| <b>Tmax - Max operating temperature</b>       | 393,15 °K    |

## ABUTMENT

|  |       |
|--|-------|
| <b>Da max - Max shoulder diameter OR</b> | 48 mm |
| <b>da min - Min shoulder diameter IR</b> | 55 mm |

