

Adapter plate OAMC-PA-G18-5

Part number: 8205195

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Material mounting bracket	Anodised aluminium
Mounting position	Any
Design	Sub-base
Operating medium	Compressed air to ISO 8573-1:2010 [-:~:-]
Corrosion resistance class CRC	2 - Moderate corrosion stress
LABS (PWIS) conformity	VDMA24364-B1/B2-L
Max. tightening torque	1 Nm
Product weight	215 g
Type of mounting	Direct mounting via thread
Suction cup mounting	Female thread G1/8
Suction cup mounting, quantity	5
Note on materials	RoHS compliant
Material seals	NBR
Material plate	Anodised wrought aluminium alloy