

Base compartment cover IP40, H: 200 mm W: 800 mm



Model	
product brand name	SIVACON S4
product designation	base compartment cover
design of the product	IP40
design of cabinet base element	for standard frame
Suitability	
suitability for interaction cable assignment	No
suitability for use for outside use	No
Appearance	
RAL color number	RAL 7035
color	light grey
product component	module incl. mounting material
• on delivery	
• ventilation	No
Mechanical Design	
height	200 mm
width	800 mm
depth	25 mm
installation width for cabinet installation	800 mm
installation depth for cabinet installation	25 mm
net weight	2.7 kg
material	sheet-steel
material thickness	1.5 mm
Approvals Certificates	
General Product Approval	other



Miscellaneous



Confirmation

Environment

[Environmental Con-
firmations](#) [Environmental Con-
firmations](#)

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8PQ2020-8BA17>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/8PQ2020-8BA17>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8PQ2020-8BA17

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

last modified:

5/26/2025 

