

Previously known as: Safe-Knit



Heat



Welding



Medium Duty

## Medium-duty welding arm sleeves, providing protection against heat, burns and cuts

- **Specialized protection:** ActivArm® 59-416 heat- and cut-resistant sleeves feature Kevlar® fabric, satisfying EN ISO B cut protection standards while guarding against heat, molten particles and sparks
- **Increased comfort:** These protective arm sleeves are also designed with a cotton internal layer that is both lightweight and breathable, which ensures sustained comfort for wearers



### Industries

- Automotive
- Metal fabrication

### Applications

- Press shop operations
- Handling metal sheets & panels
- Handling parts with sharp, rough edges
- Welding, bonding, riveting
- Handling structural and body components
- Inspection, selecting, checking parts
- Processing sheets, coils, tubes
- Cutting glasses, sheets, panels
- Handling parts in high heat areas

Previously known as: Safe-Knit

### Key Features

- **Kevlar® fabric:** Personal protection from molten particles and sparks
- **Internal cotton layer:** Lightweight, breathable comfort

### Vulcanization Chemical Accelerators

- Natural rubber proteins

Only a very small number of users may be sensitive to this ingredient(s) and hence may develop irritant and/or allergic contact reactions.

### Performance Standards & Regulatory Compliance



### Technologies

# Kevlar®

### Specifications

| BRAND   STYLE    | DESCRIPTION                                                         | Gauge | SIZE     | LENGTH      | PACKAGE                      |
|------------------|---------------------------------------------------------------------|-------|----------|-------------|------------------------------|
| ActivArm® 59-416 | <b>Liner Material:</b> Kevlar®, Cotton<br><b>Cuff Style:</b> Sleeve |       | One Size | 26" (66 cm) | 12 pieces/bag, 3 bags/carton |

For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

#### Europe, Middle East & Africa Region

Ansell Healthcare Europe NV  
Riverside Business Park  
Blvd International, 55  
1070 Brussels, Belgium  
T: +32 (0) 2 528 74 00  
F: +32 (0) 2 528 74 01

#### Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.  
Blvd. Bernardo Quintana No. 7001-C,  
Q7001 Torre II,  
Suites 1304, 1305 y 1306,  
Col. Centro Sur, c.p. 76079  
Queretaro, Qro. Mexico  
T: +52 442 248 1544 / 248 3133

#### North America Region

Ansell Healthcare Products LLC  
111 Wood Avenue South,  
Suite 900  
Iselin, NJ 08830, USA  
T: +1 800 800 0444  
F: +1 800 800 0445

#### Canada

Ansell Canada  
105 Lauder  
Cowansville, QC J2K 2K8  
Canada  
T: +1 800 363 8340  
F: +1 800 267 3551

#### Australia

Ansell Limited  
Level 3,678 Victoria Street,  
Richmond, Vic, 3121  
Australia  
T: +61 1800 337 041  
F: +61 1800 803 578

#### Asia Pacific Region

Ansell Global Trading Center  
(Malaysia) Sdn Bhd  
Prima 6, Prima Avenue  
Block 3512, Jalan Teknokrat 6  
T: +603 8310 6688  
F: +603 8310 6699