



1. CRIMPED CONTACT PIN  
HEX CRIMP SIZE .068"

RECOMMENDED  
CABLE STRIPPING DIM'S

NOTES: FINISH (PLATING THICKNESS IN MICRO-INCHES)  
 1. BRASS PER QQ-B-626  
 2. BRASS PER QQ-B-613  
 3. NICKEL PL. 100 MIN. THICK OVER COPPER STRIKE  
 4. NICKEL PL. 200 MIN. THICK OVER COPPER STRIKE  
 5. GOLD PL. 3 MIN. THICK OVER NICKEL PL. 100 MIN. THICK OVER COPPER STRIKE

DIMENSIONS ARE IN MILLIMETERS			PART NO. B1141A1-ND3G-3-75	
UNLESS OTHERWISE SPECIFIED TOLERANCES			APPROVED	DATE
0.5-6	= ±0.2			10-11-01'
6-30	= ±0.4		CHECKED	DATE
30-120	= ±0.6			10-11-01'
120-315	= ±1		DRAWN	DATE
315-1000	= ±1.6			10-11-01'
1000-2000	= ±2.4		FILE NO.	

<b>Amphenol</b>	
TITLE BNC CLAMP PLUG	
DRAWING NO. KJ-B1141A1-ND3G-59U-75	
ITEM NO.	

NO.	DESCRIPTION	MATERIAL	FINISH	Q'TY	DRAWING NO.
14	HEX NUT		NOTE 1	NOTE 3	1 B5200-14-11/65
13	WASHER		NOTE 2	NOTE 3	1 WS-10/8X05
12	GASKET	SILICONE	RED		1 B5200-12
11	BRAID CLAMP		NOTE 1	NOTE 3	1 B5200-11-65/56-B
10	RING		NOTE 1	NOTE 3	1 B5200-10
9	INSULATOR	DELTRIN	NATURAL		1 B5200-9
8	CONTACT PIN		NOTE 1	NOTE 5	1 B5200-8-21/12
7	INSULATOR	DELTRIN	NATURAL		1 B5200-7-75
6	WASHER		NOTE 2	NOTE 3	1 WS-12B/9X08
5	SPRING	SK5		NOTE 4	1 B50000-6
4	RETAINER RING		NOTE 1	NOTE 3	1 B50000-5
3	GASKET	RUBBER	RED		1 GS-115/8X15
2	BODY		NOTE 1	NOTE 3	1 B5200-2-A
1	SHELL		NOTE 1	NOTE 3	1 B50000-1-B

REVISIONS		
ISS	ZONE	DESCRIPTION\PER REQUEST\DATE