





Main

Range of product	OsiSense XC
Series name	Standard format
Product or component type	Limit switch head
Device short name	ZCE
Head type	Plunger head
Product compatibility	XCKD XCKT XCKP XCMD

Associated body	ZCMD37L2 ZCP37 ZCT26N12 ZCT28G11 ZCT27P16 ZCD25 ZCMD81L2 ZCD35 ZCP29 ZCMD21L08U78 ZCP29M12 ZCMD37L5 ZCD29M12 ZCD31 ZCP25 ZCMD39L2 ZCMD21L5 ZCD27 ZCMD69C12 ZCMD41L1 ZCMD25L5 ZCP26 ZCT26G11 ZCD28 ZCMD81L5 ZCMD29L5 ZCT25P16 ZCMD21C12 ZCT28N12 ZCP35 ZCT21G11 ZCMD29L1 ZCD39 ZCMD37L1 ZCT21N12 ZCMD25L2 ZCMD29L2 ZCP39 ZCD26 ZCP28 ZCD21M12 ZCMD61M12 ZCP21M12 ZCMD41L5 ZCT21P16 ZCT28P16 ZCD37 ZCMD81L1 ZCMD21L2 ZCP31 ZCD29 ZCP21 ZCMD39L1 ZCMD29C12 ZCT27N12 ZCMD39L5 ZCMD21L08R12 ZCT27G11 ZCMD41L2 ZCT26P16 ZCMD21M12 ZCT25N12 ZCMD25L1 ZCD21 ZCMD61C12 ZCP27 ZCT25G11 ZCMD21L1
Movement of operating head	Linear
Type of operator	Side ball bearing plunger spring return metal
Type of approach	Multi-directional approach

Complementary

Switch actuation	By 30° cam
Positive opening	Without

Environment

Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...70 °C
Environmental characteristic	Standard environment

Packing Units

Package 1 Weight	53 g
Package 2 Weight	533 g
Package 3 Weight	5.06 kg

Offer Sustainability

Sustainable offer status	Green Premium product
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------