



RATCHETING COMBINATION SPANNER SET R TOOL ROLL 10 PIECES

- 72 teeth ratchet spanners giving a 5° increment between clicks
- Reversible ratchet mechanism with hip grip & flip reverse lever
- Chrome vanadium satin finish
- Supplied in a handy tool roll style wallet
- Designed and manufactured to DIN ISO 1711-1 and DIN 3113A

Ratcheting Combination 10 Piece Spanner Set

General information

Country of origin: Taiwan
Barcode: 5020385043848
Tarriff code Europe: 8204110000
ECCN US: EAR99
ETIM: EC002209
UNSPSC: 27111711

Dimensions

Net weight (g): 1402

Attributes

Product type: Spanners & Wrench Sets
Certificates: N/A
Number of pieces: 10
Spanner type: Regular
Ratcheting: Yes
Unit of measurement: Metric
Type of set: Tool Roll

Features



DESIGNED IN SWEDEN

TengTools is a Swedish company present in more than 30 markets worldwide, and offers hand tools in smart storage solutions for demanding professionals within the automotive, maintenance and engineering sectors, as well as motor sport enthusiasts who aspire to use the same tools as top mechanics across the globe.



Sandbergsvägen 3
441 39 Alingsås, Sweden

LIST OF CONTENTS



6510RMM Ratcheting Combination Spanner Set R Tool Roll 10 Pieces

- 600510R** Ratcheting Combination Spanner Metric R 10 mm
- 600511R** Ratcheting Combination Spanner Metric R 11 mm
- 600512R** Ratcheting Combination Spanner Metric R 12 mm
- 600513R** Ratcheting Combination Spanner Metric R 13 mm
- 600514R** Ratcheting Combination Spanner Metric R 14 mm
- 600515R** Ratcheting Combination Spanner Metric R 15 mm
- 600516R** Ratcheting Combination Spanner Metric R 16 mm
- 600517R** Ratcheting Combination Spanner Metric R 17 mm
- 600518R** Ratcheting Combination Spanner Metric R 18 mm
- 600519R** Ratcheting Combination Spanner Metric R 19 mm