® IBOCO

Beta Cable Management Systems Ltd Newtown Trading Estate, Northway Lane, Tewkesbury, Gloucestershire GL20 8JG

PRODUCT

PART NUMBER

SIZE

Technical Specifications



IBOCO

T1, T1E, T1F, T1EF, TD, SEP, CL, DINBLOK, ZP!, ZP2, DNA, P1

From sizes 15mmx18mm to 150mmx100mm

SLOTTING

CAPACITY

COLOUR

SERVICE TEMPERATURE

RANGE

APPLICATION

FLAMMABILITY

FIRE HAZARD PERFORMANCE

CHEMICAL RESISTANCE

APPROVALS

STANDARDS

Up to 55% Recommended

Open and Narrow

Self extinguishing lead free PVC

Grey, White and Blue

-15°C to +65°C

UL94 V-O Rated

PRODUCTION OF THE PRODUCTION O

Ammonium Hydroxide, Chlorine, Diesel, Detergents, Ethanol, Hydrochloric acid, Inorganic solvents, Mineral oils, White spirit.

Control panel trunking for lead out of wiring through open side slots

ISO 9001, NATO A5536, IMQ, R.I.N.A., Bureau Veritas and CE

CE1, CSA, DIN43659, AFNOR, 42, CENELEC

All technical data is believed to be accurate and is provided for information and guidance only $^{\circ}$ Beta Cable Management Systems $^{\circ}$ issue 04/1 10/05

www.betacable.com

Tel +44 (0)1684 274274

Fax +44 (0)1684 276266

Beta Cable Management Systems provides the most comprehensive range of cable management systems in the UK to both the OEM and retro fit market.

