

**644487-3** SUPERSEDED

TE Internal #: 644487-3

TE Internal Description: 03P MTA100 SHRD HDR ASSY 30AU

Polyester Vertical PCB Header: 2.54mm, Shrouded, MTA 100

[View on TE.com >](#)**All Polyester Vertical PCB Header: 2.54mm, Shrouded, MTA 100 (37)**

### Product Compliance

[For compliance documentation, visit the product page on TE.com >](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2025 (247) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not lead free process capable

#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

### Customers Also Bought



TE Part #04-1270-0010  
CLWG-300-NC4



TE Part #644487-4  
04P MTA100 SHRD HDR ASSY 30AU



TE Part #1472972-1  
SSC32FAD = RLY,INTV,2P,48V,.1-



TE Part #1617003-6  
B07B332BC1 = B07 10 AMP FULL S



TE Part #5557571-1  
MJ,R/A,1X1,8P,SHD,3 GRD TABS



TE Part #745454-2  
09 RCPT ACT PIN/AP LOW SCRLK



TE Part #2007832-2  
IMP100S,H,V4P16C,UG,OEW46,4.9



TE Part #641213-6  
06P MTA100 HDR ASSY PO/ST 30AU



TE Part #3-644044-3  
03P MTA100 CONN ASSY LF

## Documents

### Product Drawings

#### 03P MTA100 SHRD HDR ASSY 30AU

English

### CAD Files

#### 3D PDF

3D

#### Customer View Model

[ENG\\_CVM\\_CVM\\_644487-3\\_H.2d\\_dxf.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_CVM\\_644487-3\\_H.3d\\_igs.zip](#)

English

#### Customer View Model

[ENG\\_CVM\\_CVM\\_644487-3\\_H.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

### Product Specifications

### Product Specification

English

---

### Agency Approvals

UL

English