

## Features

- Needle-nose pliers with long smooth jaws, suitable for gripping components in hard-to-reach areas and for delicate electronics applications.
- Steel thickness 3 mm.
- Pliers are equipped with a return spring designed to have a constant force, thus reducing operator effort.
- Ergonomic anti-slip bicomponent handle for a safe, light and comfortable grip
- Anti-reflection phosphating surface treatment.
- ESD safe version.
- Laser marking.
- Made in Italy.

## RS PRO ESD long needle-nose pliers. Medium head.

RS Stock No.: (0429686)



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

- *Made in Italy with high carbon steel and undergo a controlled atmosphere heat treatment.*
- *The anti-reflection phosphating surface treatment ensures an accurate view of the work being carried out.*
- *The tools are joined with grounded holes and surfaces, thereby allowing precise movements.*
- *The anti-slip bi-material dolphin handle is created following ergonomic principles, thus guaranteeing a safe, light and comfortable grip for the operator even when used constantly for many hours.*
- *This plier is ideal for different applications in microelectronics, jewellery making, laboratory, watch making and repairs, DIY.*
- *ESD-safe version.*

### General Specifications

|                     |                                       |
|---------------------|---------------------------------------|
| Plier Type          | Long needle-nose pliers. Medium head. |
| Tip Style           | Pointed                               |
| Serrated internally | NO                                    |
| Material            | High carbon steel                     |
| ESD Safe            | YES. Standard IEC 61340-5-1           |

### Mechanical Specifications

|                    |           |
|--------------------|-----------|
| Steel thickness    | 3 mm      |
| Hardness           | Hrc 48-50 |
| Length of the head | 32 mm     |
| Overall Length     | 160 mm    |
| Weight             | 78 g      |

