



Body protection

SHERPAHV Fluorescent yellow-Black

OUTDOOR HIGH VISIBILITY

Ultra-soft class 1 HV jacket with sherpa lining offering enhanced warmth



Specific benefits



Comfort

- Fleece lining for medium warmth



Durability

- Anti-pilling treatment



Visibility

- High visibility material meets ANSI/ISEA 107 requirements

Technologies & labels

- Segmented strip

Applications

- Building
- Finishing works / Craftsmanship
- Transportation
- Forestry
- Storage

Certifications and norms



EN 14058
1
1
0,204 (K/W)
X



EN ISO 20471
CLASS 1
X25

ANSI ISEA 107:2020
TYPE O - CLASS 1

EN ISO 13688

Protects against risks



Cold



High vis



Body protection

SHERPAHV Fluorescent yellow-Black

OUTDOOR HIGH VISIBILITY

Ultra-soft class 1 HV jacket with sherpa lining offering enhanced warmth

Standards - Details

EN14058: PROTECTIVE CLOTHING AGAINST COOL ENVIRONMENTS (-5°C AND OVER)

1 THERMAL RESISTANCE OF GARMENT CLASS (1 TO 4) RCT
1 AIR PERMEABILITY CLASS (1 TO 3) AP
0,204 RESULTANT EFFECTIVE THERMAL INSULATION
MEASURED ON A MOBILE MODEL (ICLER)
1 AIR PERMEABILITY CLASS (1 TO 3) AP

Technical details

Collection	Autumn/winter
Type of workwear	High Visibility jacket
Gender	Mixte
Size range	S → 3XL
Workwear color	Black, Yellow
Support material details	Polar padded - 100% recycled polyester
Total product weight (g/m ²)	305
Fastening	Zipper fastening
Lower sleeve	Ribbed cuff
Lower body	Ribbed cuff
Top Reflective piping	Chest (2 bands)
Number of exterior pockets	3
External pockets	3 zipped pockets
Marking type	Embroidery, Screen printing, Transfer printing
Reflective segmented tapes	yes








SHERPAHV

OUTDOOR HIGH VISIBILITY

Ultra-soft class 1 HV jacket with sherpa lining offering enhanced warmth

Protective clothing

Logistics information

Reference	Colour	Size	Designation	EAN13	Box code			Weight			
SHERJAH101FO KSM [SHEHVORPT]	Fluorescent orange-Black	S	SHERPAHV	3295249310202	13295249310209	10	1	0.0 kg	60.0 cm	40.0 cm	40.0 cm
SHERJAH101FO KMD [SHEHVORTM]	Fluorescent orange-Black	M	SHERPAHV	3295249310714	13295249310711	10	1	7.0 kg	60.0 cm	40.0 cm	40.0 cm
SHERJAH101FO KLG [SHEHVORGT]	Fluorescent orange-Black	L	SHERPAHV	3295249310721	13295249310728	10	1	7.0 kg	60.0 cm	40.0 cm	40.0 cm
SHERJAH101FO KXL [SHEHVORXG]	Fluorescent orange-Black	XL	SHERPAHV	3295249310738	13295249310735	10	1	7.0 kg	60.0 cm	40.0 cm	45.0 cm
SHERJAH101FO K2X [SHEHVORXX]	Fluorescent orange-Black	XXL	SHERPAHV	3295249310745	13295249310742	10	1	7.0 kg	60.0 cm	40.0 cm	45.0 cm
SHERJAH101FO K3X [SHEHVOR3X]	Fluorescent orange-Black	3XL	SHERPAHV	3295249310752	13295249310759	10	1	7.0 kg	60.0 cm	40.0 cm	45.0 cm
SHERJAH101FY KSM [SHEHVJAPT]	Fluorescent yellow-Black	S	SHERPAHV	3295249310189	13295249310186	10	1	7.0 kg	60.0 cm	40.0 cm	40.0 cm
SHERJAH101FY KMD [SHEHVJATM]	Fluorescent yellow-Black	M	SHERPAHV	3295249310660	13295249310667	10	1	7.0 kg	60.0 cm	40.0 cm	40.0 cm
SHERJAH101FY KLG [SHEHVJAGT]	Fluorescent yellow-Black	L	SHERPAHV	3295249310677	13295249310674	10	1	7.0 kg	60.0 cm	40.0 cm	40.0 cm
SHERJAH101FY KXL [SHEHVJAXG]	Fluorescent yellow-Black	XL	SHERPAHV	3295249310684	13295249310681	10	1	7.0 kg	60.0 cm	40.0 cm	45.0 cm
SHERJAH101FY K2X [SHEHVJAXX]	Fluorescent yellow-Black	XXL	SHERPAHV	3295249310691	13295249310698	10	1	7.0 kg	60.0 cm	40.0 cm	45.0 cm
SHERJAH101FY K3X [SHEHVJA3X]	Fluorescent yellow-Black	3XL	SHERPAHV	3295249310707	13295249310704	10	1	7.0 kg	60.0 cm	40.0 cm	45.0 cm

 Multiple sales

 Minimum sales

 Box Width

 Box Depth

 Box Height