



Fuse-link, low voltage, 15 A, AC 240 V, 16.5 kA, BS1361, 11 x 26 mm, gL/gG, BS



Powering Business Worldwide™

Part no. **15A 240V CONSUMER UNIT FUSE**
 Catalog No. **C1515**

Delivery program

Product range			Fuse
Basic function			Fuse-link
Field of application			low voltage
Rated current	I	A	15
Rated voltage			AC 240 V
Construction size			BS1361
Size			11 x 26 mm
Utilization category			gL/gG
Breaking Capacity		kA	16.5
usable for size/applications			consumer unit
Standard/Approval			BS
Shape			cylindrical
Standards/Regulations			BS1361

Technical data ETIM 7.0

Circuit breakers and fuses (EG000020) / Cylindrical fuse (EC002704)			
Electric engineering, automation, process control engineering / Electrical installation, device / Safety fuse inserts / Cylindrical fuse (safety fuse) (ecl@ss10.0.1-27-14-20-02 [AFZ797013])			
Size			Other
Rated voltage		V	240 - 240
Rated voltage			Other
Voltage type			AC
Utilization category			gL/gG (cable protection/equipment protection)
Rated operating frequency		Hz	45 - 62
Nominal current		A	15
With striker			No
Release characteristic			Other
Breaking capacity		kA	16.5