



The Professional's Choice

SAFETY DATA SHEET

1. IDENTIFICATION OF THE MATERIAL AND SUPPLIER

1.1 Product identifier

Product name 5.56 AEROSOL
Synonyms 5.56 (AEROSOL) • 5005; 5005B - PRODUCT CODE • 5027 - PRODUCT CODE • 5028 - PRODUCT CODE
• CRC 5-56 (AEROSOL) (FORMERLY) • CRC 5.56 AEROSOL

1.2 Uses and uses advised against

Uses LUBRICANT • PENETRANT

1.3 Details of the supplier of the product

Supplier name CRC INDUSTRIES (AUST) PTY LIMITED
Address 9 Gladstone Road, Castle Hill, NSW, 2154, AUSTRALIA
Telephone (02) 9849 6700
Fax (02) 9680 4914
Email info.au@crcind.com
Website www.crcindustries.com.au

1.4 Emergency telephone numbers

Emergency 13 11 26 (PIC)

2. HAZARDS IDENTIFICATION

2.1 Classification of the substance or mixture

CLASSIFIED AS HAZARDOUS ACCORDING TO SAFE WORK AUSTRALIA CRITERIA

Physical Hazards

Aerosols - Flammable: Category 1
Aerosols - Pressurised: Category 1

Health Hazards

Repeated exposure may cause skin dryness or cracking.

Environmental Hazards

Not classified as an Environmental Hazard

2.2 GHS Label elements

Signal word DANGER

Pictograms



Hazard statements

AUH066 Repeated exposure may cause skin dryness or cracking.
H222 Extremely flammable aerosol.
H229 Pressurized container: may burst if heated.

Prevention statements

P210 Keep away from heat/sparks/open flames/hot surfaces. No smoking.
P211 Do not spray on an open flame or other ignition source.
P251 Pressurized container: Do not pierce or burn, even after use.

PRODUCT NAME 5.56 AEROSOL**Response statements**

None allocated.

Storage statements

P410 + P412 Protect from sunlight. Do not expose to temperatures exceeding 50°C.

Disposal statements

None allocated.

2.3 Other hazards

No information provided.

3. COMPOSITION/ INFORMATION ON INGREDIENTS

3.1 Substances / Mixtures

Ingredient	CAS Number	EC Number	Content
DISTILLATES (PETROLEUM), HYDROTREATED LIGHT	64742-47-8	265-149-8	>60%
MINERAL OIL (SOLVENT/HIGHLY REFINED)	-	-	10 to 30%
PETROLEUM GASES, LIQUEFIED (<0.1% 1,3-BUTADIENE)	68476-85-7	270-704-2	10 to 30%
CORROSION INHIBITOR(S)	-	-	<10%

4. FIRST AID MEASURES

4.1 Description of first aid measures

Eye	If in eyes, hold eyelids apart and flush continuously with running water. Continue flushing until advised to stop by a Poisons Information Centre, a doctor, or for at least 15 minutes.
Inhalation	If inhaled, remove from contaminated area. To protect rescuer, use a Type A (Organic vapour) respirator or an Air-line respirator (in poorly ventilated areas). Apply artificial respiration if not breathing.
Skin	If skin or hair contact occurs, remove contaminated clothing and flush skin and hair with running water. Continue flushing with water until advised to stop by a Poisons Information Centre or a doctor.
Ingestion	For advice, contact a Poisons Information Centre on 13 11 26 (Australia Wide) or a doctor (at once). If swallowed, do not induce vomiting. Ingestion is considered unlikely due to product form.
First aid facilities	None allocated.

4.2 Most important symptoms and effects, both acute and delayed

See Section 11 for more detailed information on health effects and symptoms.

4.3 Immediate medical attention and special treatment needed

Treat symptomatically.

5. FIRE FIGHTING MEASURES

5.1 Extinguishing media

Dry agent, carbon dioxide or foam. Prevent contamination of drains and waterways.

5.2 Special hazards arising from the substance or mixture

Extremely flammable aerosol. May evolve toxic gases (carbon oxides, hydrocarbons) when heated to decomposition. Aerosol may explode at temperatures exceeding 50°C. Eliminate all ignition sources, including cigarettes, open flames, spark producing switches/tools, heaters, pilot lights, mobile phones, etc when handling. Aerosol cans may explode above 50°C.

5.3 Advice for firefighters

Evacuate area and contact emergency services. Toxic gases may be evolved in a fire situation. Remain upwind and notify those downwind of hazard. Wear full protective equipment including Self Contained Breathing Apparatus (SCBA) when combating fire. Use waterfog to cool intact containers and nearby storage areas.

5.4 Hazchem code

2YE	
2	Fine Water Spray.
Y	Risk of violent reaction or explosion. Wear full fire kit and breathing apparatus. Contain spill and run-off.
E	Evacuation of people in and around the immediate vicinity of the incident should be considered.

6. ACCIDENTAL RELEASE MEASURES

6.1 Personal precautions, protective equipment and emergency procedures

Wear Personal Protective Equipment (PPE) as detailed in section 8 of the SDS. Clear area of all unprotected personnel. Ventilate area where possible.

6.2 Environmental precautions

Prevent product from entering drains and waterways.

6.3 Methods of cleaning up

Contain spillage, then cover / absorb spill with non-combustible absorbent material (vermiculite, sand, or similar), collect and place in suitable containers for disposal.

6.4 Reference to other sections

See Sections 8 and 13 for exposure controls and disposal.

7. HANDLING AND STORAGE

7.1 Precautions for safe handling

Before use carefully read the product label. Use of safe work practices are recommended to avoid eye or skin contact and inhalation. Observe good personal hygiene, including washing hands before eating. Prohibit eating, drinking and smoking in contaminated areas.

7.2 Conditions for safe storage, including any incompatibilities

Store in a cool (< 50°C), dry, well ventilated area, removed from incompatible substances, heat or ignition sources and foodstuffs. Ensure aerosol containers/ cans are adequately labelled, protected from physical damage and sealed when not in use. Check regularly for damaged/ leaking containers. Large storage areas should have appropriate fire protection systems.

7.3 Specific end uses

No information provided.

8. EXPOSURE CONTROLS / PERSONAL PROTECTION

8.1 Control parameters

Exposure standards

Ingredient	Reference	TWA		STEL	
		ppm	mg/m ³	ppm	mg/m ³
Liquefied petroleum gas (LPG)	SWA [AUS]	1000	1800	1000	1800
Mineral Oil Mist	SWA [AUS]	--	5	--	--

Biological limits

No biological limit values have been entered for this product.

8.2 Exposure controls

Engineering controls

Avoid inhalation. Use in well ventilated areas. Where an inhalation risk exists, mechanical explosion proof extraction ventilation is recommended. Flammable vapours may accumulate in poorly ventilated or confined areas. Vapours are heavier than air and may travel some distance to an ignition source and flash back.

PPE

Eye / Face	Wear splash-proof goggles.
Hands	Wear nitrile or neoprene gloves.
Body	When using large quantities or where heavy contamination is likely, wear coveralls.
Respiratory	At high vapour levels, wear a Type A-Class P1 (Organic gases/vapours and Particulate) respirator.



9. PHYSICAL AND CHEMICAL PROPERTIES

9.1 Information on basic physical and chemical properties

Appearance	AMBER LIQUID (AEROSOL DISPENSED)
Odour	PLEASANT ODOUR
Flammability	EXTREMELY FLAMMABLE
Flash point	< 0°C (Propellant)
Boiling point	193°C (Initial)
Melting point	NOT AVAILABLE
Evaporation rate	NOT AVAILABLE
pH	NOT AVAILABLE
Vapour density	> 1 (Air = 1)
Specific gravity	0.81
Solubility (water)	INSOLUBLE
Vapour pressure	NOT AVAILABLE
Upper explosion limit	12 %
Lower explosion limit	1.4 %
Partition coefficient	NOT AVAILABLE
Autoignition temperature	550°C
Decomposition temperature	NOT AVAILABLE
Viscosity	NOT AVAILABLE
Explosive properties	NOT AVAILABLE
Oxidising properties	NOT AVAILABLE
Odour threshold	NOT AVAILABLE

9.2 Other information

% Volatiles	82 %
-------------	------

10. STABILITY AND REACTIVITY

10.1 Reactivity

Carefully review all information provided in sections 10.2 to 10.6.

10.2 Chemical stability

Stable under recommended conditions of storage.

10.3 Possibility of hazardous reactions

Polymerization is not expected to occur.

10.4 Conditions to avoid

Avoid heat, sparks, open flames and other ignition sources.

10.5 Incompatible materials

Incompatible with oxidising agents (e.g. hypochlorites), acids (e.g. nitric acid), alkalis (e.g. sodium hydroxide), heat and ignition sources.

10.6 Hazardous decomposition products

May evolve toxic gases (carbon oxides, hydrocarbons) when heated to decomposition.

11. TOXICOLOGICAL INFORMATION

11.1 Information on toxicological effects

Acute toxicity Based on available data, the classification criteria are not met. This product may have the potential to cause adverse health effects if intentionally misused (e.g. deliberately inhaling contents).

Information available for the ingredients:

Ingredient	Oral LD50	Dermal LD50	Inhalation LC50
DISTILLATES (PETROLEUM), HYDROTREATED LIGHT	> 2000 mg/kg (rat)	> 2000 mg/kg (rabbit)	--

Skin Not classified as an irritant. Contact may result in mild irritation, drying and defatting of the skin, rash and dermatitis.

Eye Not classified as an eye irritant. Contact may cause discomfort, lacrimation and redness.

Sensitisation Not classified as causing skin or respiratory sensitisation.

Mutagenicity Not classified as a mutagen.

PRODUCT NAME 5.56 AEROSOL

Carcinogenicity	Not classified as a carcinogen.
Reproductive	Not classified as a reproductive toxin.
STOT - single exposure	Not classified as causing organ damage from single exposure. However, over exposure may result in mild irritation of the nose and throat, with coughing. High level exposure may result in dizziness, nausea and headache.
STOT - repeated exposure	Not classified as causing organ damage from repeated exposure.
Aspiration	Ingestion is considered unlikely due to product form.

12. ECOLOGICAL INFORMATION**12.1 Toxicity**

No information provided.

12.2 Persistence and degradability

No information provided.

12.3 Bioaccumulative potential

No information provided.

12.4 Mobility in soil

No information provided.

12.5 Other adverse effects

No information provided.

13. DISPOSAL CONSIDERATIONS**13.1 Waste treatment methods**

Waste disposal	For small amounts, absorb contents with sand or similar and dispose of to an approved landfill site. Do not puncture or incinerate aerosol cans. Contact the manufacturer/supplier for additional information (if required).
Legislation	Dispose of in accordance with relevant local legislation.

14. TRANSPORT INFORMATION

CLASSIFIED AS A DANGEROUS GOOD BY THE CRITERIA OF THE ADG CODE



	LAND TRANSPORT (ADG)	SEA TRANSPORT (IMDG / IMO)	AIR TRANSPORT (IATA / ICAO)
14.1 UN Number	1950	1950	1950
14.2 Proper Shipping Name	AEROSOLS	AEROSOLS	AEROSOLS
14.3 Transport hazard class	2.1	2.1	2.1
14.4 Packing Group	None allocated.	None allocated.	None allocated.

14.5 Environmental hazards

No information provided.

14.6 Special precautions for user

Hazchem code	2YE
GTEPG	2D1
EmS	F-D, S-U

15. REGULATORY INFORMATION

15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

Poison schedule	A poison schedule number has not been allocated to this product using the criteria in the Standard for the Uniform Scheduling of Medicines and Poisons (SUSMP).
Classifications	Safework Australia criteria is based on the Globally Harmonised System (GHS) of Classification and Labelling of Chemicals.
Inventory listings	AUSTRALIA: AIC (Australian Inventory of Industrial Chemicals) All components are listed on AIC, or are exempt.

16. OTHER INFORMATION

Additional information AEROSOL CANS may explode at temperatures approaching 50°C.

RESPIRATORS: In general the use of respirators should be limited and engineering controls employed to avoid exposure. If respiratory equipment must be worn ensure correct respirator selection and training is undertaken. Remember that some respirators may be extremely uncomfortable when used for long periods. The use of air powered or air supplied respirators should be considered where prolonged or repeated use is necessary.

PERSONAL PROTECTIVE EQUIPMENT GUIDELINES:

The recommendation for protective equipment contained within this report is provided as a guide only. Factors such as form of product, method of application, working environment, quantity used, product concentration and the availability of engineering controls should be considered before final selection of personal protective equipment is made.

HEALTH EFFECTS FROM EXPOSURE:

It should be noted that the effects from exposure to this product will depend on several factors including: form of product; frequency and duration of use; quantity used; effectiveness of control measures; protective equipment used and method of application. Given that it is impractical to prepare a report which would encompass all possible scenarios, it is anticipated that users will assess the risks and apply control methods where appropriate.

Abbreviations

ACGIH	American Conference of Governmental Industrial Hygienists
CAS #	Chemical Abstract Service number - used to uniquely identify chemical compounds
CNS	Central Nervous System
EC No.	EC No - European Community Number
EMS	Emergency Schedules (Emergency Procedures for Ships Carrying Dangerous Goods)
GHS	Globally Harmonized System
GTEPG	Group Text Emergency Procedure Guide
IARC	International Agency for Research on Cancer
LC50	Lethal Concentration, 50% / Median Lethal Concentration
LD50	Lethal Dose, 50% / Median Lethal Dose
mg/m ³	Milligrams per Cubic Metre
OEL	Occupational Exposure Limit
pH	relates to hydrogen ion concentration using a scale of 0 (high acidic) to 14 (highly alkaline).
ppm	Parts Per Million
STEL	Short-Term Exposure Limit
STOT-RE	Specific target organ toxicity (repeated exposure)
STOT-SE	Specific target organ toxicity (single exposure)
SUSMP	Standard for the Uniform Scheduling of Medicines and Poisons
SWA	Safe Work Australia
TLV	Threshold Limit Value
TWA	Time Weighted Average

PRODUCT NAME 5.56 AEROSOL

Report status

This document has been compiled by RMT on behalf of the manufacturer, importer or supplier of the product and serves as their Safety Data Sheet ('SDS').

It is based on information concerning the product which has been provided to RMT by the manufacturer, importer or supplier or obtained from third party sources and is believed to represent the current state of knowledge as to the appropriate safety and handling precautions for the product at the time of issue. Further clarification regarding any aspect of the product should be obtained directly from the manufacturer, importer or supplier.

While RMT has taken all due care to include accurate and up-to-date information in this SDS, it does not provide any warranty as to accuracy or completeness. As far as lawfully possible, RMT accepts no liability for any loss, injury or damage (including consequential loss) which may be suffered or incurred by any person as a consequence of their reliance on the information contained in this SDS.

Prepared by

Risk Management Technologies
5 Ventnor Ave, West Perth
Western Australia 6005
Phone: +61 8 9322 1711
Fax: +61 8 9322 1794
Email: info@rmt.com.au
Web: www.rmtglobal.com

[End of SDS]