

Smart camera



PRODUCT DATA

Resolution:	1920 x 1080 (2 MP)
IR night vision:	8 - 10 m
Frame rate:	FHD 15 fps, HD 25 fps
Features:	PIR motion sensor, micro SD card slot up to 64 GB
Pan and tilt range:	355° / 155°
Operational temperature:	-20°C to 60°C
Wi-Fi frequency:	2.4 GHz
Network protocol:	IEEE 802.11 b/g/n
Compatibility:	APP: DELTACO SMART HOME, Amazon Alexa & Google Home
Package contents:	Smart camera with attached USB-cable, power adapter, screws and manual

2 MP
With PTZ
Wi-Fi 2.4 GHz
PIR-motion sensor
Built in mic & speaker



LOGISTICS DATA

Article number:	SH-IPC04
Brand:	DELTACO
EAN code:	7333048041890
Country of origin:	China
Custom tariff number:	85258019
Master carton packing unit:	20 pcs
Master carton gross weight:	8,82 kg
Master carton dimensions:	285 x 410 x 465 mm
Package type:	Box
Package weight:	0,368 kg
Package dimensions:	120 x 180 x 87 mm
Article weight:	225 g
Article dimensions:	70 x 70 x 150 mm

