



Nano Mam - For

Electrical performance:
CEI EN 50393 as applicable
(testing under water head
of the accessory installed in a box)

Gel: UL 94-HB

Operating temperature

Installation temperature:
-40°C / +50°C

Fully submersible

Can be used underground

IPX8
OFFICIALLY
TESTED | **IMQ**

Pre-filled gel accessories to seal, protect and make safe electrical connections. Inclusive of connectors.

- Ready to use, quick, re-enterable!
- Ideal for outdoor & underground installations, fully submersible
- Immediately energizable
- For rigid or flexible insulated wires from 1 a 4 mm²
- For 1, 2 or 3 cores connections
- Small, compact and resistant
- No shelf life
- Halogen free
- UV resistant



NANO FOR 2,5

NANO FOR 4

NANO MAM 4

*Kit with end connectors/
terminal blocks*

Kit with terminal blocks

NANO MAM 2,5



Nano Mam 2,5


Product	Formation and wires cross section (Max N° x mm ²)	Combination	Pieces for package	A x B x C (mm)
Nano Mam 2,5	3 x 1 - 2,5	3 through	2 pcs/ Blister	36 x 37 x 26



With one connector included for each Nano Mam

Nano Mam 4

Product	Formation and wires cross section (Max N° x mm ²)	Combination	Pieces for package	A x B x C (mm)
Nano Mam 4	3 x 1,5 - 4	3 through	1 pcs/ Blister	52 x 53 x 29



With one connector included for each Nano Mam

Nano For 2,5

Product	Formation and wires cross section (Max N° x mm ²)	Combination	Pieces for package	A x B x C (mm)
Nano For 2,5	3 x 1 - 2,5	3 connections / In/Out	1 pcs/ Blister	33 x 52 x 26



With one connector included for each Nano For

Nano For 4

Product	Formation and wires cross section (Max N° x mm ²)	Combination	Pieces for package	A x B x C (mm)
Nano For 4	3 x 1 - 4	3 connections / In/Out	1 pcs/ Blister	52 x 53 x 29



With one connector included for each Nano For

