



Gamma Mini



- Ultra slim modern polycarbonate wall/ceiling light suitable for education and residential applications and ancillary areas
- Matt white finish to body and diffuser with optional chrome trim ring
- Rear fixing bracket and terminal housing for ease of installation
- Non-dimmable

General Information

Lamp Type	LED
IP Rating	IP54
IK Rating	IK09
Class Protection	2
Internal / External	Internal / External
Surface / Recessed / Suspended	Surface
Warranty (Years)	3
Material	Polycarbonate



Technical Information

Wattage	11W
Lumens Delivered	1000lm
Lm/W	94lm/W
Beam Angle	110
CRI	80
CCT	4000K
Input	220/240V
Hertz	50/60Hz
Operating Temp	-5°C to 35°C
Lumen Depreciation	L70 54,000h
Power Factor	0.9

