



Pushing Performance
Since 1945

Han 22HPR slim HTE-SL-3xM32-M20



Image is for illustration purposes only. Please refer to product description.

Part number	19 40 022 0471
Specification	Han 22HPR slim HTE-SL-3xM32-M20
HARTING eCatalogue	https://harting.com/19400220471

Identification

Category	Hoods / Housings
Series of hoods/housings	Han [®] HPR slim
Type of hood/housing	Hood

Version

Size	22 HPR
Version	Top entry
Number of cable entries	4
Cable entry	1x M20 3x M32
Locking type	Screw locking
Field of application	Hoods/housings for harsh environments

Technical characteristics

Tightening torque	10 Nm Fixing screws 15 Nm PE screw
Tightening torque (screw locking)	4 Nm
Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP66 IP68 IP69 / IPX9K acc. to ISO 20653



Pushing Performance
Since 1945

Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Powder-coated
Colour (hood/housing)	RAL 9005 (jet black)
Material (locking)	Stainless steel

Specifications and approvals

Specifications	IEC 61984
	IEC 60664-1

Commercial data

Packaging size	1
Net weight	885 g
Country of origin	China
European customs tariff number	85389099
GTIN	5713140831339
eCl@ss	27440202 Shell for industrial connectors
ETIM	EC000437
UNSPSC 24.0	39121466