



— PRODUCT DATA SHEET

HF4



HF4

PRODUCT DESCRIPTION

The compact Ledlenser HF4 is perfect for tackling jobs around the house, gardening or any job that requires a little extra illumination. Light up the darkest of attics or the shadowy corners of a garden shed using the spot beam for longer distances and the flood light for close-up work. To help maintain night vision, there's also a handy red front light. With the HF4, users are never left in the dark, as it runs on both disposable and rechargeable batteries - particularly useful if a power cut knocks out the electricity. Incorporating recycled materials and backed by a 7-Year warranty for complete peace of mind, the Ledlenser HF4 is designed with a brighter future in mind for all.



- Compact headlamp with spot for long-range and flood light for close-up illumination
- Additional red front light to preserve night vision
- Dual Power Source: Operates with rechargeable and disposable batteries (3x AAA alkaline batteries included)
- Sustainable: Use of recycled materials¹³ and 7-year warranty*
- Element-proof: High water and dust resistance (IP67)

TECHNICAL DATA	
Weight incl. batteries [g]	102
Material	PC
Headband material	Elastic textile
Headband type	Side
Head movement type	Stepless Movement
Head movement angle [°]	55
Headband specifications	Detachable, Elastic, Washable

POWER SUPPLY	
Battery quantity	3
Rechargeable	No
Battery type	Alkaline
Total battery voltage [V]	1.5
Total battery capacity [mAh]	1100
Total battery energy [Wh]	1.65 Wh
Useable batteries	AAA NiMH 1.2V, Polymer USB-C 1350mAh
Energy status indicator	Battery Indicator, Low Battery Warning

SWITCH	
Top Switch	

FURTHER SPECIFICATIONS	
IP class	IP67
Drop test (drop height) [m]	1.5
Working temperature range [°C]	-20 to +40

LIGHT FUNCTIONS	
Cool White Main: Boost, Power, Mid power, Low power	

LIGHT SOURCE	MAIN
Amount LEDs	2
Colour	Cool White
Colour temperature [K]	6000 to 7500
Colour rendering index (CRI)	70

LIGHT VALUES - Cool White Main				
	Boost	Power	Mid power	Low power
Light output [lm]	450	300	100	20
Beam distance [m]	110	100	60	20
Run time [h]	-	2.5	10	40

FEATURES AND TECHNOLOGIES	
Backup Mode, Flicker Free, Transportation Lock, Memory Function, Red Light, Dual Power Source, Multi-Lens Technology, Temperature Control System	

HF4

PACKAGING AND LOGISTICS

PACKAGING INFORMATION

Type of packaging	Box
Scope of delivery	Connect Adapter - HF 2026, 1 set of batteries (AAA)
Item No.	503316
Colour	Black
Customs tariff number	CTN_85131000

SINGLE PACKAGE

Dimensions W x H x D [cm]	14.5 x 8.5 x 4.2
Gross weight [g]	171
GTIN-13	4058205042642

EXPORT CARTON

Dimensions W x H x D [cm]	37.5 x 17 x 31
Gross weight [g]	4764
GTIN-13	4058205042635

PACKAGING INFORMATION

Type of packaging	Box
Scope of delivery	Connect Adapter - HF 2026, 1 set of batteries (AAA)
Item No.	503343
Colour	Smoly Blue
Customs tariff number	CTN_85131000

SINGLE PACKAGE

Dimensions W x H x D [cm]	14.5 x 8.5 x 4.2
Gross weight [g]	171
GTIN-13	4058205043359

EXPORT CARTON

Unit	24
Dimensions W x H x D [cm]	37.5 x 17 x 31
Gross weight [g]	4764
GTIN-13	4058205043342

RRP PRICING	RRP ex.VAT	RRP inc.VAT
STERLING	£29.13	£34.95
EURO	€32.48	€39.95

PACKAGING INFORMATION

Type of packaging	Box
Scope of delivery	Connect Adapter - HF 2026, 1 set of batteries (AAA)
Item No.	503303
Colour	Forest Green
Customs tariff number	CTN_85131000

SINGLE PACKAGE

Dimensions W x H x D [cm]	14.5 x 8.5 x 4.2
Gross weight [g]	171
GTIN-13	4058205042307

EXPORT CARTON

Unit	24
Dimensions W x H x D [cm]	37.5 x 17 x 31
Gross weight [g]	4760
GTIN-13	4058205042321

HF4

PRODUCT SERIES

Reveal the world: With a Ledlenser HF headlamp, what was once hidden comes into view. Details emerge that demand your attention, beauty appears where shadows once concealed it, and the adventure or challenge ahead becomes unmistakably clear. Because at Ledlenser, light is more than illumination, it's revelation.

FOOTNOTES

The information pertaining to scope of delivery, appearance, performance, dimensions and weight corresponds to the information available at the time of publication. In the interest of product development, we reserve the right to change scope of delivery, appearance, design and color without prior notice. Product images may vary from the actual products and may show optional accessories which can be purchased separately. Errors and omissions excepted.