



Main

Commercial Status	Commercialised
Range	Linerigy
Product name	FH
Product or component type	Comb busbar
Accessory / separate part category	Connection accessory
Poles description	4P
Number of ways	6 ways, type : N + 3 L with 18 mm pitch
Distance between way	72 mm
Poles distribution	N L1 L2 L3
Connector type	Tooth
Length in 18 mm modules	24

Complementary

Device presentation	Cuttable
[In] rated current	100 A (40 °C)
[Ue] rated operational voltage	415 V AC
[Ui] rated insulation voltage	500 V AC conforming to IEC 61439-2
Mounting mode	Horizontal
9 mm pitches	48
Width	430 mm
Colour	Anthracite grey (RAL 7016)
Range compatibility	Acti 9
Product compatibility	IC60 IID ISW-NA IK60 IID K ISW switch disconnecter

Environment

Standards	IEC 60947-7-1 IEC 61439-2
Fire resistance	960 °C (30 s) conforming to IEC 60695-2-1