



Application	Commercial, Education, Healthcare, Hospitality, Industrial, Retail
Specification	Performance

Merlin

Merlin Emergency Downlight Non-Maintained White

Code: AMED/1/W/3NM



PRODUCT FEATURES

- Ultra-low profile recessed self-test emergency downlight
- High specification optic design and performance allows increased spacing providing reduced cost
- Self-test as standard with DALI emergency option
- Supplied with open area and escape route interchangeable lenses
- Available in black and white finishes
- Up to 17.8 metres spacing between luminaires

GENERAL INFORMATION

Wattage	5W
Lumens Delivered	248lm (Escape Route) 274lm (Open Area)
Beam Angle	110
CRI	70
CCT	6000-7000K
Input	220-240V
Operating Temp	0°C - 40°C
SDCM	6
Cut-Out Size	75
Product Weight without Packaging	0.694 kg

TECHNICAL INFORMATION

Light Source	LED
Colour / Finish	White
IP Rating	IP20
IK Rating	IK08
Class Protection	1
Internal / External	Internal
Surface / Recessed / Suspended	Recessed
Warranty (Years)	7
CE Mark	Yes
Diameter	85 mm
Emergency Output Duration	3 Hr



Application	Commercial, Education, Healthcare, Hospitality, Industrial, Retail
Specification	Performance

Merlin

Merlin Emergency Downlight Non-Maintained White

Code: AMED/1/W/3NM

