

IP65 FLEXIBLE LED TAPE +FLEX 208



12.7W/M



up to
1815LM/M



IP65



Recycleable
Cardboard



>80Ra



3000K, 4000K
6000K



38.45mm
Cut Points



FEATURES

- Available in three different colour temperatures
- Industrial grade adhesive backing tape
- Humidity 40% - 70% RH
- Working temperature -20°C - +45°C
- High efficacy
- 3 years warranty

SPECIFICATIONS

Stock Code	0991-251	1053-421	1592-974
Part Code	C0-2-208-65	D0-2-208-65	F0-2-208-65
Voltage	24VDC	24VDC	24VDC
Power Consumption	12.7 W/M	12.7 W/M	12.7 W/M
Lumen Output	1777LM/M	1777LM/M	1815LM/M
Efficacy	140LM/W	140LM/W	143LM/W
Tone (CCT)	3000K ●	4000K ●	6000K ●
LED/metre	208	208	208
LED Pitch	4.81mm	4.81mm	4.81mm
Cut Points	38.45mm	38.45mm	38.45mm
CRI	>80Ra	>80Ra	>80Ra
IP Rating	65	65	65
Dimensions	5000 x 8 x 2.2mm	5000 x 8 x 2.2mm	5000 x 8 x 2.2mm



3000K



4000K



6000K

IP65 FLEXIBLE LED TAPE +FLEX 208



COMPATIBILITY



CONTROL METHODS

- Bluetooth (Apps, Voice Control) - BLE-15A
- Remote Control - SCD107W

SUGGESTED DRIVERS

Up to 1 M	Up to 5 M	Up to 10 M
Power supplied from ONE end	Power supplied from ONE end	Power supplied from the MIDDLE or BOTH ends
Non Dimmable	Non Dimmable	Non Dimmable
PCV2420	PCV2475	PCV24151
Mains Dimmable	Mains Dimmable	Mains Dimmable
UVC2425TD	UVC24100TD	UVC24200ETD
DALI Dimmable	DALI Dimmable	DALI Dimmable
DA-30-24	DA-75-24	ELG-150-24DA

*IP rated and other options available. Contact us for more information.

MECHANICAL DIAGRAM

