



PRODUCT-DETAILS

UPS PowerValue 11T G2 2 kVA B

UPS PowerValue 11T G2 2 kVA B



General Information

Extended Product Type	UPS PowerValue 11T G2 2 kVA B
Product ID	4NWP100161R0001
EAN	7640169261909
Catalog Description	UPS PowerValue 11T G2 2 kVA B
Long Description	VFI online double conversion;1800W;9min;RS232;USB;mini COM slot

Material Compliance

Conflict Minerals Reporting Template (CMRT)	9AKK108467A5658
REACH Declaration	4NWD005611
RoHS Information	4NWD005610 rev.B
RoHS Status	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019
SCIP	90637fca-ce67-49e0-89b3-c3fbd7890322 Switzerland
Simplified SCIP	cb559433-f28a-486b-9113-d5b1159c3f6e Spain ee9f0f68-0259-47fe-9e79-027f3cfbd81c Belgium 03e7fdf0-630d-497b-822e-13518de9f6f2 Netherlands decc3ed2-a430-44fc-a568-abf4e90f97e6 Hungary 8ee4bdc7-8970-4f94-baba-cae7375787e7 Czech Republic 2631a6fc-e08a-4b4d-89f4-0ec38ff5f26d Croatia

6fb5f3b4-dcdb-49b2-af6e-2338af1b51de	Germany
8ed5a9d4-b87a-4b01-888f-91dd77ba58dc	Estonia
b9343948-0318-4137-8107-3c086fe67547	Greece
65222795-94d2-4cd5-b477-a958264616e7	Germany
18048e1c-7afd-413b-90ad-26e88c430815	Sweden
3916b312-d4b6-4791-a1f0-221ae61bd8f9	Germany
87f2d8c2-ae04-42a6-ad91-a114c169f2a7	Germany
258441ce-144d-4bce-9926-992a6dcb3030	Denmark
16d8d188-2ceb-4752-afb9-78ac930009b4	Belgium
dfe9082e-89e6-4038-bbb6-c88b744ab31b	Portugal
9fab881a-2327-40a6-a487-f978f39c420e	France
10ff7b30-e41a-4370-aed0-a17cabe407fa	Sweden
2a237794-ae6b-441c-8205-0ed2175a725c	Poland
8cf8c869-a9a4-42e2-b858-d109f5338aa4	Finland
ece2bfcd-ee8b-4876-8a45-bd7da2a23aa1	Germany
444b2b85-7bb6-4531-a267-1cffca3560ba	France
adff9c98-8fbf-432b-a144-d3b1cb4a35fa	Poland
b7d814df-cca9-4d6c-af8c-b57866032a18	Norway
4d781575-e689-4584-8829-dd5ae1042a96	Bulgaria
0ef8ae13-4153-446f-9a64-4ec8e0128795	Poland
8e312077-2dc7-45e7-b6ff-863b241730d4	Hungary

Popular Downloads

Data Sheet, Technical Information	4NWD003883_EN
Instructions and Manuals	4NWD003883_EN

Environmental

Ambient Air Temperature	Storage -15...+60 °C
Environmental Information	No declaration needed

Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85044000
E-Number (Finland)	8408611
E-Number (Norway)	6609402
E-Number (Sweden)	5257247
Country or Territory of Origin	China

Dimensions

Product Net Width	190 mm
Product Net Height	327 mm
Product Net Depth / Length	399 mm
Product Net Weight	13.3 kg

Container Information

Package Level 1 Units	box 1 piece
Package Level 1 Width	324 mm
Package Level 1 Height	464 mm
Package Level 1 Depth / Length	500 mm
Package Level 1 Gross Weight	19.6 kg
Package Level 1 EAN	7640169261909

Technical

Apparent Power Output	2000 V·A
Battery Chemical Composition	Lead-Acid
Battery Type	Portable
Battery Weight	2.5 kg
Communication Interface	USB, RS-232
Connection Type	IEC C14
Display Type	LCD
Input Voltage (U _{in})	220 V 230 V 240 V
Input Voltage Type	AC
Number of Batteries	4
Number of Outputs	C13 Connection 4
Number of Phases	1-phase Primary 1-phase Secondary
Options Provided	Auto shut down function Potential free switch contact Network-management
Rated Frequency (f)	Primary 50 Hz Primary 60 Hz Secondary 50 Hz Secondary 60 Hz
Rated Output Power	1800 W

Certificates and Declarations

Declaration of Conformity - CCC	No certification needed
Declaration of Conformity - CE	4NWD004828

External Classifications and Standards

ETIM 9	EC000382 - UPS
ETIM 10	EC000382 - UPS
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
WEEE B2C / B2B	Business To Business
CN8	85044000
eClass	V11.1 : 27040690
Object Classification Code	G

Categories

UPS, Power Conditioning and Power Distribution → UPS → Single-Phase UPS → PowerValue 11 T G2 IEC 230V

