

Datasheet

RS Pro Plain Stainless Steel Pan Head Machine Screws, M6 x 20mm

RS Stock No: **189-535**



Product Details

RS Pro machine screw measuring M6 x 20 mm, is made of type 316 S16 plain A4 grade 18//8 stainless steel, which has higher level of corrosion resistance than A2 stainless steel. The pan head screw is perfect for use at up to 300°C. This slotted drive screw is suitable for use in food, medical, chemical, construction and electronic applications.

Features and Benefits

- A4 grade 18/8 stainless steel (Type 316 S16) construction
- Higher level of corrosion resistance than A2 S/S
- Suitable for use up to 300°C
- Suitable for use in most food, medical, chemical, construction and electronic applications



ENGLISH

Specifications:

Drive Type	Slot
Finish	Plain
Head Shape	Pan
Material	Stainless Steel
Length	20 mm
Stainless Steel Type	316 (A4)
Thread Pitch	1
Thread Size (Metric)	M6
Head Diameter	6.8 to 11.57 mm
Head Height	3.3 to 3.6 mm
Slot Depth	1.4 mm
Slot Width	1.6 mm
Specification	DIN 85