

8179A
Lifting round slings, orange, 10 t, high-tenacity polyester (PES) belt

CE

EN 1492-2



	art.	L m	WLL ton	H mm
081790502	8179A 1-T10	1	10	95
081790503	8179A 1,5-T10	1,5	10	95
081790504	8179A 2-T10	2	10	95
081790505	8179A 2,5-T10	2,5	10	95
081790506	8179A 3-T10	3	10	95
081790508	8179A 4-T10	4	10	95
081790510	8179A 5-T10	5	10	95
081790512	8179A 6-T10	6	10	95
081790516	8179A 8-T10	8	10	95
081790520	8179A 10-T10	10	10	95
081790524	8179A 12-T10	12	10	95
081791204	8179A 2-T12	2	12	100
081791205	8179A 2,5-T12	2,5	12	100
081791206	8179A 3-T12	3	12	100
081791207	8179A 3,5-T12	3,5	12	100
081791208	8179A 4-T12	4	12	100
081791209	8179A 4,5-T12	4,5	12	100
081791210	8179A 5-T12	5	12	100
081791211	8179A 5,5-T12	5,5	12	100
081791212	8179A 6-T12	6	12	100
081791213	8179A 6,5-T12	6,5	12	100
081791214	8179A 7-T12	7	12	100
081791215	8179A 7,5-T12	7,5	12	100
081791216	8179A 8-T12	8	12	100
081791217	8179A 8,5-T12	8,5	12	100
081791218	8179A 9-T12	9	12	100
081791219	8179A 9,5-T12	9,5	12	100
081791220	8179A 10-T12	10	12	100
081791504	8179A 2-T15	2	15	110
081791505	8179A 2,5-T15	2,5	15	110
081791506	8179A 3-T15	3	15	110
081791507	8179A 3,5-T15	3,5	15	110
081791508	8179A 4-T15	4	15	110
081791509	8179A 4,5-T15	4,5	15	110
081791510	8179A 5-T15	5	15	110
081791511	8179A 5,5-T15	5,5	15	110
081791512	8179A 6-T15	6	15	110
081791513	8179A 6,5-T15	6,5	15	110
081791514	8179A 7-T15	7	15	110
081791515	8179A 7,5-T15	7,5	15	110
081791516	8179A 8-T15	8	15	110
081791517	8179A 8,5-T15	8,5	15	110
081791518	8179A 9-T15	9	15	110
081791519	8179A 9,5-T15	9,5	15	110
081791520	8179A 10-T15	10	15	110
081792004	8179A 2-T20	2	20	130
081792005	8179A 2,5-T20	2,5	20	130
081792006	8179A 3-T20	3	20	130
081792007	8179A 3,5-T20	3,5	20	130
081792008	8179A 4-T20	4	20	130
081792009	8179A 4,5-T20	4,5	20	130
081792010	8179A 5-T20	5	20	130
081792011	8179A 5,5-T20	5,5	20	130
081792012	8179A 6-T20	6	20	130
081792013	8179A 6,5-T20	6,5	20	130