

FEATURES

- 3W LED PCB
- 3-hour minimum emergency duration
- Includes legend kit
- Ni-Cad rechargeable battery
- Impact resistant polycarbonate diffuser
- Painted steel body with polycarbonate
- Can be wired for maintained or non-maintained operation
- Constant light output
- Dimensions: 393mm x 191mm x 65mm

LED Emergency Lighting Bulkhead 3 W

RS Stock No.: 795-9372



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

This LED emergency exit lighting bulkhead offers an energy saving and cost effective solution to fulfil emergency lighting requirements. This box is wired as maintained, but it can also be wired as non-maintained if required. It is an ideal replacement for the old style halogen emergency exit fittings

General Specifications

Lamp Type	LED
Light Style	Bulkhead
Luminosity	120lm
Maintained	Maintained
Legend	Supplied with running legend and arrow pointing up
Material	Aluminium + Polycarbonate
Finish	White body with green/clear diffuser
Duration	3h
Lamp Supplied	Yes
Applications	LED emergency exit signs are ideal for commercial, industrial and retail applications and can be found in: Corridors, Workshops, Emergency exits

Electrical Specifications

Wattage	3W
Voltage Rating	230V
Battery	3.6V 110mAh NiCd

Mechanical Specifications

Length	393mm
Width	191mm
Depth	65mm
Fitting Type	Bulkhead

Protection Category

IP Rating	IP20
------------------	------

Approvals

Compliance/Certifications	RoHS
Standards Mets	EN 60598-1: 2008+A11: 2009, EN 60598-2-22: 1998+A1: 2003+A2:2008, EN 55015: 2013, EN 61000-3-2: 2006+A2: 2009, EN 61000-3-3: 2013, EN 61547: 2009
EU Energy Efficiency Rating	A+



