

# OCS HP 100806 TRANS - Outdoor housing



1471774

<https://www.phoenixcontact.com/gb/products/1471774>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Outdoor housing, color: light gray, dimensions: 276 x 257 x 185 mm (10" x 8" x 6"), incl. corner inlays, cover plugs, screws, cover: transparent, plastic latch, material: PC UV-stabilized

## Your advantages

- Internationally certified housing system
- Special plastic enables safe continuous operation
- Provides protection against the ingress of jet water
- Withstands even heavy mechanical strain

## Commercial data

Item number	1471774
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	ACFDBA
Product key	ACFDBA
GTIN	4063151880729
Weight per piece (including packing)	1.759 kg
Weight per piece (excluding packing)	1.759 kg
Customs tariff number	84879090
Country of origin	EE

# OCS HP 100806 TRANS - Outdoor housing



1471774

<https://www.phoenixcontact.com/gb/products/1471774>

## Technical data


### Notes

Assembly note	Only use the screws provided to screw the components onto the corner inlays, the mounting pillars, and the housing.
Recommendation	To maintain the degree of protection, you must install suitable components with at least the same IP degree of protection in all openings.
Recommendation	Further information and detailed dimensions are available in the download area.
Order information:	Mounting feet, mounting plates, mounting panels, and the mount for mast mounting are available as accessories, but are not supplied as standard.

### Product properties

Product type	Complete housing
Housing type	Outdoor housing
Housing series	OCS
Product family	OCS..1008..
Type	Complete housing with transparent cover incl. mounting material
Ventilation openings present	no
Battery compartment	no

### Dimensions

Dimensional drawing	
Width	257 mm
Height	276 mm
Depth	185 mm
Hole diameter	10 mm (Can be secured mechanically with the latch)

### Material specifications

Color (Housing)	light gray (RAL 7035)
Color (Housing cover)	transparent
Material (Housing)	PC UV stabilized
Material (Seal)	PUR
Flammability rating according to UL 94	V2
Surface characteristics	untreated

### Environmental and real-life conditions

# OCS HP 100806 TRANS - Outdoor housing



1471774

<https://www.phoenixcontact.com/gb/products/1471774>

## Glow-wire test

Specification	IEC 60695-2-11:2014-02
Temperature	850 °C
Time of exposure	30 s

## Degree of protection (IP code)

Specification	IEC 60529:2001-02
---------------	-------------------

## Ambient conditions

Max. IP code to attain	IP69
Max. NEMA code to attain	6P
Impact strength	IK10 (at -35°C ... +40°C)
Ambient temperature (operation)	-40 °C ... 80 °C

## PCB data

Type of PCB mount	Bolt mounting
-------------------	---------------

## Mounting


Mounting type	Mast mounting or panel mounting
Mounting position	any

## Packaging specifications

Type of packaging	Box packaging
-------------------	---------------


## Drawings

Dimensional drawing



Schematic representation – for additional information, see product range drawing in the Download Center


Diagram



Power dissipation diagram for 0 K ... 100 K

1471774

<https://www.phoenixcontact.com/gb/products/1471774>



Power dissipation diagram for 0 K ... 30 K


# OCS HP 100806 TRANS - Outdoor housing



1471774

<https://www.phoenixcontact.com/gb/products/1471774>

## Approvals

 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/1471774>



**cULus Listed**

Approval ID: E255026-20221017

# OCS HP 100806 TRANS - Outdoor housing



1471774

<https://www.phoenixcontact.com/gb/products/1471774>

## Classifications

### ECLASS

ECLASS-13.0	27190103
-------------	----------

### ETIM

ETIM 9.0	EC001031
----------	----------

1471774

<https://www.phoenixcontact.com/gb/products/1471774>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	faea8fa8-2d45-4cb0-9f03-fd062a501545

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd  
Halesfield 13, Telford  
Shropshire, TF7 4PG  
01952 681700  
[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)