



# 60182

## MINIATURE CIRCUIT BREAKER 240V 30A



[Download your 60182 datasheet](#)



[Characteristics](#) | Documents & Downloads

### Main

Hide

Device application	Distribution
Range of product	C60
Product or component type	Miniature circuit-breaker
Device short name	C60 UL489
Poles description	3P
Number of protected poles	3
[In] rated current	30 A at 25 °C
Trip unit technology	Thermal-magnetic
Curve code	C
Breaking capacity	6 kA Icu conforming to IEC 60947-2 - 440 V AC 10 kA AIR conforming to UL 489 - 240 V AC 10 kA Icu conforming to IEC 60947-2 - 415 V AC 20 kA Icu conforming to IEC 60947-2 - 240 V AC
Suitability for isolation	Yes conforming to IEC 60947-2

### Complementary

Hide

[Ue] rated operational voltage	12...240 V AC 125 V DC 60 V DC
Magnetic tripping limit	7...10 x In
Contact position indicator	Yes
Control type	Operating handle
Local signalling	Positive break indication
Mounting mode	Fixed
Mounting support	35 mm symmetrical DIN rail
9 mm pitches	6
Height	107 mm
Width	54 mm
Depth	73 mm
Product weight	0.33 kg
Colour	Grey
Mechanical durability	20000 cycles
Electrical durability	10000 cycles
Connections - terminals	Tunnel type terminals 2.5...35 mm <sup>2</sup> max
Tightening torque	3.5 N.m


### Environment

Hide

Standards	IEC 60947-2 UL 489 CSA C22.2 No 5.2
-----------	---

<b>IP degree of protection</b>	IP40 IEC 60529
<b>Tropicalisation</b>	2
<b>Relative humidity</b>	95 % 55 °C
<b>Operating altitude</b>	2000 m
<b>Ambient air temperature for operation</b>	-30...70 °C
<b>Ambient air temperature for storage</b>	-40...80 °C

### Offer Sustainability [-] Hide

<b>Sustainable offer status</b>	Green Premium product
<b>RoHS (date code: YYWW)</b>	Compliant - since 0640 - Schneider Electric declaration of conformity
<b>REACH</b>	Reference not containing SVHC above the threshold
<b>Product environmental profile</b>	Available  <a href="#">download Product environmental</a>
<b>Product end of life instructions</b>	Need no specific recycling operations

### Contractual warranty [-] Hide

<b>Period</b>	18 months
---------------	-----------