



Operating temperature	-40-105 °C
Flammability rating (UL94)	V2

### **Dimensions:**

Max. AWG-size	Other
Min. AWG-size	20
Nominal cross section (device side)	0.5-4 mm <sup>2</sup>
Nominal cross section (installation side)	0.5-4 mm <sup>2</sup>
Cable diameter	1-4 mm
Conductor cross section flexible (fine-strand) with cable end sleeve	0.5-2.5 mm <sup>2</sup>
Conductor cross section solid (solid, stranded)	0.5-2.5 mm <sup>2</sup>
Width	14 mm
Height	11 mm
Strip length	12 mm
MOQ	25 .
Unit	pcs
Nominal cross section	0.5-4 mm <sup>2</sup>
Length	42 mm
Nominal voltage	450 V

### **Approvals:**

Approved according to CE	Yes
Approved according to TUV	Yes
Approved according to UKCA	Ja

### **Compliance:**

Conflict Minerals	N/A, Contains no conflict minerals
REACH	No SVHC (Latest. 04 Feb 2026)
RoHS	RoHS 3 (2015/863)
SCIP	Not Applicable
US TSCA	No (5 PBT Subs, Feb 2021)

### **Other information:**

ETIM-Class	EC000446 - Screwless terminal
ETIM-Release	9.0
Trademark	NEMIQ
Product Group	102014
Search Description	SKV2025EJ, ENR2025H, EFO2025H
Alternative SKU	SCD-40525-S
E-no	E1441361

### **Logistic information:**

---

<b>Barcode</b>	733117641965
<b>Country of origin</b>	CN
<b>E-no</b>	E1441361
<b>Item status</b>	Stock item, normally in stock with reservation for in between sales.
<b>MOQ</b>	25 .
<b>Stock code</b>	SCD-4 0525-S
<b>Taric code</b>	85369010
<b>Unit</b>	pcs

---

\*We reserve the right to make technical changes and disclaim any typographical errors.

---

Nelco Contact AB - Daléns Gata 7, 195 61 Arlandastad, Sweden - Tel. +46 (0)8 754 70 40 - [order@nelco.se](mailto:order@nelco.se) - [www.nelco.se](http://www.nelco.se)