# **WE/WEP**

**Signal Tower** 








# Ultra slim half-moon shaped Signal Tower offers seamless integration with most equipment.

#### **FEATURES**


- Clear vertical-cut lens for enhanced illumination over a wide perspective.
- Has an optional built-in audible alarm (FB type) with an output of 90dB (at 1m).
- Installation can be vertical or horizontal.
- Two body color selections of chrome plated or ivory white.
- · Lens made of superior impact and heat resistant polycarbonate resin for superior durability and enhanced illumination.
- Both NPN and PNP Compatible for direct connection to a PLC (24V DC ONLY)
- Two lighting patterns of flashing and continuous lighting.
- Dust and water resistance rating of IP65 (except for FB type: IP54).
- · Available colors are in Red, Amber, Green, Blue, and Clear/White.
- Has the CE mark and conforms to the requirements for the EC directive.
- Is a UL Recognized Component (File No. E215660).

# 37.5mm Super-thin Design!



Patlite has perfected a 37.5mm-thin design that significantly enhances integration with the equipment as a built-in signal system.

# **Exclusively New LED Lighting Design**




Patlite has created a revolutionary patented lighting design in which multiple LEDs project light across a broad peripheral area, ensuring equal intensity at the sides as well as the front. This design, with its side-projection technology, is a unique achievement in signal light design.

# Dimensions (Unit: mm)



# How to Order



# **Specifications**


| Stack Number | Model       | Rated Voltage | Power Consumption | Mass |
|--------------|-------------|---------------|-------------------|------|
| 3 Tiers      | WE(P)-302   |               | 1.7W              | 260g |
|              | WE(P)-302FB | 302FB 2       |                   | 300g |
| 4 Tiers      | WE(P)-402   | AC/DC 24V     | 2.0W              | 310g |
|              | WE(P)-402FB | AC/DC 24V     | 3.2W              | 350g |
| 5 Tiers      | WE(P)-502   |               | 2.7W              | 310g |
|              | WE(P)-502FB |               | 3.7W              | 350g |


# Signal Line voltage and current per LED Module


| Alawa Carrada | Lead Wire Color | 1        |        |           |             | LED                 |         | Alarm              |                   |
|---------------|-----------------|----------|--------|-----------|-------------|---------------------|---------|--------------------|-------------------|
| Alarm Sounds  | Lead Wire Color |          | Model  | Rated     | Signal Line | Signal Line Current |         | Cianal Lina Invish | Inviteb           |
| Buzzer 1      | Buzzer 1 Purple |          | Model  | Voltage   | Voltage     |                     |         |                    | Inrush<br>Current |
| 2 4 = 2 4 1   | · I· ·          | <b>!</b> |        |           |             | R, Y                | G, B, C | Current            | Current           |
| Buzzer 2      | Skyblue         |          | WE/WEP | AC/DC 24V | AC/DC 24V   | 30mA                | 25mA    | 40mA               | 250mA             |

# Wiring


# AC/DC 24V Lighting Type









### DC 24V NPN Type




# DC 24V NPN FB Type



# AC/DC 24V Lighting/Flashing Type



### DC 24V PNP Type



#### DC 24V PNP FB Type

