

LED RECHARGEABLE HEADLAMP

Product Specifications

SPECIFICATIONS	OBS-HL1
Color	Grey/Black/Red
Material	Aluminum/Plastic
Luminosity (Lumen)	500 (All Lamps) 400 (Spot - High Mode) 120 (Spot - Low Mode) 200 (Flood)
Rechargeable	Yes
Battery Type	Lithium-Ion or AAA (3)
Runtime	1.2h (All Lamps) 2h (Spot - High Mode) 10h (Spot - Low Mode) 4h (Flood)
Charge Time	2.5h
Charging Port	USB-C
Weight	4.0 oz / 112.5 g
Length	2.7 in / 68 mm
Width	1.5 in / 39 mm
Height	1.6 in / 40 mm
Storage/Operating Temperature	+15°F to +120°F / -10°C to +50°C
IP Rating	IP54
IK Rating	IK07
Headband	Yes
Easily Removeable Headlamp Body	Yes
Motion Sensor	Yes
Accessories	Charging Cable