




## BL2-12/20/A





Item number 63.9358-\*

20-pole socket strips, consisting of 2 rows of 10 sockets with solder connection. No need for individual mounting of sockets: Simplified panel drilling, orientation of solder connections and compact mounting with only 5 screws. Available with socket spacing of 6 mm.

Technical data	
Diameter of plug system	2 mm
Rated Values	30 VAC, 10 A / 60 VDC, 10 A
Surface treatment electrical contact	Au
Base material electrical contact	CuZn
Colours *	21 22 23 24 25
Test accessory acc. to	IEC EN 61010-2-030
Number sockets	2 x 10
Remarks	Other colors available on request.