



The cable glands SKINTOP® MS-M ATEX are sufficient to the requirements of explosion protection to equipment-group II and equipment category 2G and 1D, type of protection Increased Safety “e”. (in acc. to EN 60079-0, EN60079-7, EN 61241-1).

Application Range



Technical Data

Material: Body: Nickel Plated Brass
 Insert: Polyamide
 Seal: CR
 O Ring: NBR
 Locknut: Nickel Plated Brass

Protection Rating: IP68

Temperature Range: -30°C to +100°C

Approvals

UL File No. E79903

EC Type Examination Certification: IBExU 01 ATEX 1041x

IECEX Certificate: IECEX IBE 13.0026x

Article List

RS Part Number	Description	Thread Size	Clamping Range (mm)	Spanner Wrench (mm)	Overall Length (mm)	Thread Length (mm)
433-0967	ATEX Brass Cable Gland	M25	9 – 17	29	38.5	8