

AB622 - Cut C13 PU Essential Multipack (Pk12)

Collection: Cut Resistant

Range: Hand Protection

Materials: HPPE, Elastic, Glass Fibre, Polyester

Dipping:

Outer Carton: 12

Product information

Our level C cut-resistant glove is perfect for protection against cuts and sharp objects. The seamless liner ensures added comfort and dexterity, while the EN407 contact heat level 1 provides short-term protection against temperatures up to 100°C. This glove is a streamlined version of our flagship A622 glove, with reduced packaging and single-colour branding, providing a more economical choice. Sold in packs of 12 for maximum value.



Hand Protection

A wide and increasing range of hand protection products is available. In order to help cater to every need. Only the best materials and manufacturing methods are used in the production of Portwest's extensive range of Hand Protection products....

Standards

EN ISO 21420: 2020 Dexterity 5
EN 388: 2016 + A1: 2018 (4X43C)
EN 407: 2020 (X1XXXX)

Features

- Sold in pack of 12 pairs for great value
- Level C cut resistance
- 13 gauge liner constructed for durability and precise fitting
- Smooth PU coating for increased abrasion resistance
- Protection against contact heat up to 100°C
- Palm dipped to increase dexterity and ventilation
- CE certified
- UKCA marked

PORTWEST[®]



AB622 - Cut C13 PU Essential Multipack (Pk12)

Commodity Code: 6116108091

Test House

SATRA Technology Europe Ltd (Notified Body No.: NB: 2777)
Bracetown Business Park
D15 YN2P, Ireland
Cert No: 2777/25828-01/E00-00

Carton Dimensions/Weight

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m ³)	EAN13	GTIN/DUN14
AB622G7RS	Grey	58.0	38.0	29.0	0.7050	0.0639	5036146018826	15036108894038
AB622G7RM	Grey	58.0	38.0	29.0	0.7400	0.0639	5036146018819	15036108894021
AB622G7RL	Grey	58.0	38.0	29.0	0.8020	0.0639	5036146018802	15036108894014
AB622G7RXL	Grey	58.0	38.0	29.0	0.8420	0.0639	5036146018833	15036108894045
AB622G7RXXL	Grey	58.0	38.0	29.0	0.9300	0.0639	5036146018840	15036108894052