



Figure similar

SITOR fuse link, with Bolt-on links, NH00, In: 100 A, gR, Un AC: 690 V, Un DC: 440 V, front indicator

| Model                                                                  |  |                                                                             |             |
|------------------------------------------------------------------------|--|-----------------------------------------------------------------------------|-------------|
| product brand name                                                     |  | SETRON                                                                      |             |
| product designation                                                    |  | SITOR fuse link                                                             |             |
| design of the product                                                  |  | with angle connector                                                        |             |
| design of an identification indicator                                  |  | front indicator                                                             |             |
| design of the switching contact                                        |  | with M8 bolt-on links. mounting dimension: 80 mm. for screwing onto busbars |             |
| design of the fuse link                                                |  | SITOR, LV HRC design                                                        |             |
| General technical data                                                 |  |                                                                             |             |
| size of fuse system according to EN 60269-1                            |  | NH00                                                                        |             |
| operating class of the fuse link                                       |  | gR                                                                          |             |
| type of voltage of the operating voltage                               |  | AC/DC                                                                       |             |
| Supply voltage                                                         |  |                                                                             |             |
| supply voltage                                                         |  |                                                                             |             |
| • at AC                                                                |  | 690 V                                                                       |             |
| • at DC                                                                |  | 440 V                                                                       |             |
| Breaking Capacity                                                      |  |                                                                             |             |
| switching capacity current                                             |  |                                                                             |             |
| • at DC according to IEC 60947-2 rated value                           |  | 50 kA                                                                       |             |
| • according to IEC 60947-2 rated value                                 |  | 100 kA                                                                      |             |
| Dissipation                                                            |  |                                                                             |             |
| power loss [W]                                                         |  | 29 W                                                                        |             |
| power loss [W]                                                         |  |                                                                             |             |
| • for rated value of the current at AC in hot operating state per pole |  | 29 W                                                                        |             |
| • maximum                                                              |  | 29 W                                                                        |             |
| Product details                                                        |  |                                                                             |             |
| product description                                                    |  | with bolt-on links, silver-plated                                           |             |
| accessories included                                                   |  | no                                                                          |             |
| Mechanical Design                                                      |  |                                                                             |             |
| mounting position                                                      |  | Any, preferably vertical                                                    |             |
| net weight                                                             |  | 205 g                                                                       |             |
| Environmental conditions                                               |  |                                                                             |             |
| ambient temperature during operation                                   |  |                                                                             |             |
| • minimum                                                              |  | -20 °C                                                                      |             |
| • maximum                                                              |  | 50 °C                                                                       |             |
| environmental category                                                 |  | -20 to +50 at 95% relative humidity                                         |             |
| Approvals Certificates                                                 |  |                                                                             |             |
| General Product Approval                                               |  | other                                                                       | Environment |



EG-Konf.



UR



[Confirmation](#)

[Environmental Con-  
firmations](#)

## Environment

[Environmental Con-  
firmations](#)

## Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3NE8021-3MK>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3NE8021-3MK>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=3NE8021-3MK](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NE8021-3MK)

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>





