

FEATURES

- Nitrile rubber O-Ring cord
- Diameter of 2.62 mm
- Length of 8.5 m
- Minimum operating temperature of -30°C (special consideration is required for use below this temperature)
- Maximum operating temperature of +120°C (continuous) or +150°C (intermittent)

RS PRO Nitrile Rubber O-Ring Cord, 2.62mm Diam. , 8.5m Long

RS Stock No.: 138-1601



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

If you're in need of a handy and reliable way to make tight, leak-proof seals for your machinery, this nitrile rubber O-Ring cord from the RS PRO range is a useful addition to your supplies. This O-Ring cord delivers a leak-proof seal by creating a vacuum between two surfaces. With a diameter of 2.62 mm and a length of 8.5 m, the cord is easy to cut to different lengths to make several, differently sized O-Rings. Its nitrile rubber material is robust enough to withstand temperatures as low as -30°C or as high as +120°C. It's also safe for use at intermittent temperatures of up to +150°C.

General Specifications

Material	Nitrile Rubber
----------	----------------

Mechanical Specifications

Diameter	2.62mm
Length	8.5m

Operation Environment Specifications

Operating Temperature Range	-30°C to 120°C
-----------------------------	----------------

Approvals

Compliance/Certifications	EN61340
---------------------------	---------



RS Stock No	Description	Diameter	Length	Material
138-1599	O-Ring Cord, Dia. 1.78mm x 8.5m	1.78 mm	8.5 Metres	Nitrile Rubber
138-1600	O-Ring Cord, Dia. 2mm x 8.5m	2.0 mm	8.5 Metres	Nitrile Rubber
138-1601	O-Ring Cord, Dia. 2.62mm x 8.5m	2.62 mm	8.5 Metres	Nitrile Rubber
138-1602	O-Ring Cord, Dia. 3.5mm x 8.5m	3.5 mm	8.5 Metres	Nitrile Rubber
138-1604	O-Ring Cord, Dia. 4.0mm x 8.5m	4.0 mm	8.5 Metres	Nitrile Rubber
138-1605	O-Ring Cord, Dia. 4.5mm x 8.5m	4.5 mm	8.5 Metres	Nitrile Rubber
138-1606	O-Ring Cord, Dia. 5mm x 8.5m	5.0 mm	8.5 Metres	Nitrile Rubber
138-1607	O-Ring Cord, Dia. 5.33mm x 8.5m	5.33 mm	8.5 Metres	Nitrile Rubber
138-1608	O-Ring Cord, Dia. 6mm x 8.5m	6.0 mm	8.5 Metres	Nitrile Rubber
138-1609	O-Ring Cord, Dia. 7mm x 8.5m	7.0 mm	8.5 Metres	Nitrile Rubber
138-1610	O-Ring Cord, Dia. 8mm x 8.5m	8.0 mm	8.5 Metres	Nitrile Rubber