


Features

- FeCu-Ni "J" Type Thermocouples
- Max. operating temperature 200°C
- ½" Fittingnut
- Protection tube AISI304(DIN1.4301) Stainless Steel
- Sensor type DIN/IEC-584 "J" FeCu-Ni
- Immersion Length 50mm
- Tube Diameter 6mm

RS PRO Bayonet Valve "J" Type Thermocouples With ½" Fittingnut

RS Stock No. 0350357



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

Bayonet Valve "J" Type Thermocouples Temperature Sensor

Diameter(M): 6mm

Immersion Length(L): 50mm

Applications Fields

- Machinery Manufacturing
- Panel Manufacturing
- Production and Test Equipment
- Food, Chemical, Textile Sectors
- Industrial Control Applications


General Specifications

Max. Operating Temperature	-50 °C / +200 °C
Sensor type	"J" Type Thermocouples (DIN/IEC-584)
Protection tube material	AISI304(DIN1.4301) Stainless Steel
Connector	½" Fittingnut

Mechanical Specifications

Diameter (M)	6mm
Immersion Length (L)	50mm

Electrical Connection



Thermoelement Connections

