



Aluminium oxide shop roll cloth SBR width 38 mm x length 25 m A80 for general use

Aluminium oxide shop roll cloth SBR width 38 mm x length
25 m A80 for general use

Item number: 45016408

EAN: 4007220602041

The cloth-backed variant is suitable for general, heavy-duty use on alloyed and non-alloyed steels, as well as non-ferrous metals.

The carton has a tear-off edge for separating the sections of abrasive belt at the workplace.

Technical information

Abrasive	Aluminium oxide A
Dia. hole	75 mm
Grit size	80
Length	25 m
PFERD TOOLS type	SBR 38
Width	38 mm

Advantages

- ✔ Highly flexible, enabling optimal adjustment to the contour.
- ✔ Little wear due to high tear strength and very good grain adhesion.

Recommendations for use

- ✔ Trim to the necessary size if required.

Ordering notes

- ✔ Please order shop roll holder separately.

Materials that can be worked

- ✓ Aluminium
- ✓ Annealed cast iron
- ✓ Brass
- ✓ Bronze
- ✓ Cast steel
- ✓ Cobalt-based alloys
- ✓ Copper
- ✓ Fibre-reinforced thermosetting plastics (GRP, CRP)
- ✓ Grey/nodular cast iron (GG/GJL, GGG/GJS)
- ✓ Hardened, heat-treated steels over 1.200 N/mm² (< 38 HRC)
- ✓ Nickel-based alloys (e.g. Inconell and Hastelloy)
- ✓ Stainless steel (INOX)
- ✓ Steel materials with a hardness > 54 HRC
- ✓ Steels up to 1,200 N/mm² (< 38 HRC)
- ✓ Thermoplastics
- ✓ Titanium
- ✓ Titanium alloys
- ✓ Zinc

Applications

- ✓ Cleaning
- ✓ Roughening
- ✓ Step-by-step fine grinding
- ✓ Surface work

Drive types

- ✓ Manual application
-

**PFERD
TOOLS**



August Rüggeberg GmbH & Co. KG
Hauptstraße 13
51709 Marienheide

+49 2264 9-0

+49 2264 9-400

info@pferd.com