



PRODUCT-DETAILS

PK28/M25/A

STR NPB/Q FITTING M25 28MM-MET



General Information	
Extended Product Type	PK28/M25/A
Product ID	7TCA296100R0080
EAN	5020963016042
Catalog Description	STR NPB/Q FITTING M25 28MM-MET
Long Description	3/4 Inch Nickel Plated Brass Straight Conduit Fitting with Fixed External Threads, Metric Thread Size M25

Additional Information	
Product Main Type	Adaptaflex Flexible Cable Protection
Application	For Insertion into Threaded Entries or Knockout to Connect Conduit

Ordering	
EAN	5020963016042
UPC	786210243573

Technical

Number of Batteries	0
Color	Metallic
Material	Brass
Size	3/4 Inch

Environmental

WEEE Category	Product Not in WEEE Scope
RoHS Information	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019

Container Information

Package Level 1 Units	10 piece
Package Level 1 EAN	5020963016042
Package Level 1 Height	11.81 in 300 mm
Package Level 1 Depth / Length	1 in 25 mm
Package Level 1 Width	7.87 in 200 mm

Certificates and Declarations

Declaration of Conformity - CE	9AKK107492A9618
RoHS Declaration	9AKK107992A8994
REACH Declaration	9AKK107992A8994

External Classifications and Standards

ETIM 8	EC001176 - Screw connection for corrugated plastic hose
ETIM 9	EC001176 - Screw connection for corrugated plastic hose
UNSPSC	39121311

Categories

Low Voltage Products and Systems → Installation Products → Cable Protection, Explosion Proof and Lighting → Flexible Cable Protection Systems

