



PIC-3 0525-PP8

Topplämma, 3-ledare, 0.5-2.5mm², push-in, enkelrad 8st/frp



Product Properties:

Number of clamp positions (device side)	3 .
Type of locking/unlocking	Push
Nominal voltage	450 V
Nominal current	24 A
Suitable for solid conductors	Yes
Transparent	Yes
Number of clamp positions	3 .
With operation lever	No
Suitable for solid core	Yes
Suitable for flexible core	Yes
Suitable for multi-wire core	Yes
Strip length	10 mm
Colour	Orange
Operating temperature	-40-105 °C
Connector type	Terminal Block
Flammability rating (UL94)	V2

Dimensions:

Max. AWG-size	12
Min. AWG-size	Other
Nominal cross section (device side)	0.5-2.5 mm ²
Nominal cross section (installation side)	0.5-2.5 mm ²
Cable diameter	1-4 mm

Conductor cross section flexible (fine-strand) with cable end sleeve	0.5-1.5 mm ²
Conductor cross section solid (solid, stranded)	0.5-2.5 mm ²
Width	16 mm
Height	7 mm
Strip length	10 mm
MOQ	10 .
Unit	pck
Nominal cross section	0.5-2.5 mm ²
Length	16 mm
Nominal voltage	450 V

Approvals:

Approved according to CE	Yes
Approved according to TUV	Yes
Approved according to UKCA	Ja

Compliance:

Conflict Minerals	N/A, Contains no conflict minerals
REACH	No SVHC (Latest. 04 Feb 2026)
RoHS	RoHS 3 (2015/863)
SCIP	Not Applicable
US TSCA	No (5 PBT Subs, Feb 2021)

Other information:

ETIM-Class	EC000446 - Screwless terminal
ETIM-Release	9.0
Trademark	NEMIQ
Product Group	Terminal Blocks
Alternative SKU	PIC-30525-PP8

Logistic information:

Barcode	733117643293
Country of origin	CN
Item status	Stock item, normally in stock with reservation for in between sales.
MOQ	10 .
Stock code	PIC-3 0525-PP8
Taric code	85369010
Unit	pck

*We reserve the right to make technical changes and disclaim any typographical errors.

