

CASES
1620
Case



Peli protector cases - Waterproof peli cases - 1620 case



Interior dimensions:
54.3 x 41.4 x 31.9 cm (21" x 16" x 13")

Watertight, crushproof, and dust proof

- Easy-open, double-step latches
- Open cell core with solid wall design - strong, light weight
- O-ring seal
- Automatic Pressure Equalization Valve
- Fold down handles
- Stainless steel hardware and padlock protectors
- 4 layer Pick 'N' Pluck™ foam with convoluted lid foam
- Personalised nameplate service available
- Unconditionally Guaranteed

Retractable extension handle

Strong polyurethane wheels with stainless steel bearings



Black

Peli protector cases - Waterproof peli cases - 1620 case SPECIFICATIONS

| Exterior Dimensions (L x W x D) | | Interior Dimensions (L x W x D) | |
|--|------------------------|--|--|
| 63 x 49.2 x 35.2 cm (25" x 19" x 14") | | 54.3 x 41.4 x 31.9 cm (21" x 16" x 13") | |
| Lid Depth | Bottom Depth | Total Depth | |
| 5.2 cm (2") | 26.7 cm (10.50") | 31.9 cm 12.56") | |
| Lid Depth | Bottom Depth | Total Depth | |
| 5.2 cm (2.06") | 26.7 cm (10.50") | 31.9 cm 12.56") | |
| Weight w/Foam | Weight w/o Foam | Buoyancy Max. | |
| 11.8 kg. (26.01 lbs) | 11.1kg (24.47 lbs.) | 68 kg (149.91 lbs.) | |
| Range Temperature | No. of Wheels | Retractable Handle | |
| -40 / 99° C (-40 / 210° F) | 2 | Yes | |

Personalized Nameplate Available

1620EU Case Certificates

- IP67(1 meter submersion for 30 minutes)
- MIL C-4150J
- Def Stan 81-41/STANAG 4280

Materials

| Body | Latch | Lid O-Ring | Pins |
|------------------------|------------|---------------------------------------|------------------------|
| Polypropylene | ABS | PolymerStainless Steel | |
| Foam | Purge Body | Purge Vent | Purge O-Ring |
| 1.3 lb Polyurethane | ABS | 3 Micron Hydrophobic Non-Woven PET | 70 Shore Nitrile |

Configuration

| Cat. # | Description |
|--------|--|
| 1620EU | Peli protector cases - Waterproof peli cases - 1620 case |
| | |
| | |

Peli protector cases - Waterproof peli cases - 1620 case Accessories

No accessories are currently available for this product