

Datasheet

## RS Pro PET D-sub Connector Backshell, 9 Way, Strain Relief

RS Stock No: **544-3402**



### Product Details

RS Pro screwdown cover with jackscrews has 9 number of contact with E D-sub shell size in a PET housing. This straight screwdown cover is suitable for metal shell D-connectors and is supplied with 2 standard jack screws, 2 finger operated jack screws, steel internal cable clamp with side or top cable entry.

### Features and Benefits

- PET housing
- Offers locking action with jack screws in combination with female screwlock assembly
- Side or top cable entry via removable knockouts and cable retention

**Specifications:**

Body Orientation	Straight
Colour	Black
Housing Material	PET
Number of Contacts	9
Strain Relief	Yes
Dimensions	40.9 x 34.5 x 16.3 mm
Operating Temperature Range	-20 to +75°C
Standards Met	UL 94V-0