


Features

- FeCu-Ni "J" Type Thermocouples
- Max. operating temperature 200°C
- Protection tube AISI304(DIN1.4301) Stainless Steel
- Sensor type DIN/IEC-584 "J" Type
- Cable type Silicone+Silicone
- Tube Diameter 6mm
- Immersion Length 60mm
- Cable Length 2meter

RS PRO Bayonet Bore "J" Type Thermocouples

RS Stock No: 0350439



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

Standard Bayonet "J" Type Thermocouples Temperature Sensor

Diameter(M): 6mm

Immersion Length(L): 60mm

Cable Length(K): 2m

Applications Fields

- Machinery Manufacturing
- Panel Manufacturing
- Production and Test Equipment
- Food, Chemical, Textile Sectors
- Industrial Control Applications


General Specifications

Max. Operating Temperature	0 °C / +200 °C
Standard cable types	Silicone+Silicone
Sensor type	"J" Type Thermocouples (DIN/IEC-584)
Protection tube material	AISI304 (DIN1.4301) Stainless Steel

Mechanical Specifications

Diameter (M)	6mm
Immersion Length (L)	60mm
Cable Length (K)	2m

Electrical Connection



Thermoelement Connections

