

Professionally approved products.

## Screwdriver

# 7 Pc Hex Precision Screwdriver Set



[RS Stock No. 243-686](#)

### Material

Screwdriver tip: Silicone chrome Molybdenum Vanadium steel (svcm55)

Handles: Polypropylene / TPR double injection.

### Finish

Screwdriver tip: Satin chrome finish with Phosphate Black tip

Handle: Black colour TPR grip and Red colour (Pantone-187c) P.P. injection handle.

### Hardness

Screwdriver: Heat treated to HRC: 55~59 degrees



## Professionally approved products.

### Contents

7 pc - Hex precision screwdriver with Black colour TPR grip and Red P.P injection shaft & handle (Remove the magnet from the steel tip)

### Size

Hex:

0.6 x 60 mm

0.7 x 60 mm

1.3 x 60 mm

1.5 x 60 mm

2.0 x 60 mm

2.5 x 100 mm

3.0 x 100 mm

### Remark

Torque, dimensions and gauge tests meet DIN-ISO 2936 standard

### Features

1. Screwdriver tip made from high grade chrome Vanadium steel
2. Rotating cap allows user to drive easily and adjust precisely
3. Provides comfortable grip during rotation

