



ENGLISH

## Screwdriver Sets

# 45 PCS Precision Screwdriver Set



[RS Stock No. 668-5723](#)



### Material

Chrome molybdenum steel (cr-mo#8660) for hex / torx / slotted / ph/pz.  
Chrome vanadium steel (6150) for nut screwdriver bits and extendable blade, high carbon steel for open spanner  
P.S. For magnifier and gripping handle ,alum handle

### Finish

Chrome plate finish for bits

### Hardness

Heat treated to HRC 54~58 for bits and HRC 38~48 for precision nut spinner screwdriver bits

### Contents

**1pc**-Extentable alum bit driver handle

**30pc**-Precision screwdriver bits 28mm length

Slotted: 1.0, 1.5, 2.0, 2.5, 3.0, 3.5, 4.0

Phillips: 000, 00 ,0,1

Pozi: 0, 1

Star: t4, t5, t6, t7, t8, t9, t10, t15, t20

Hexagon: 0.7, 0.9, 1.3, 1.5, 2.0, 2.5, 3.0, 4.0

**6pc**- Precision nut screwdriver bits: 2.5, 3.0, 3.5, 4.0, 4.5, 5.0mm

**5pc**- Precision open-end wrench screwdriver bits