
0170 : Adjustable wrench with reversible jaw













The + product :

Reversible jaw: 1 side for pipes, 1 side for nuts.

Wide opening: the jaw opens wider than wrenches with equivalent length.

For confined spaces: thin nose tips.

Description

The two-in-one tool: High quality reversible jaw, with one serrated side for tightening and loosening pipes and damaged nuts, and one smooth side for usual work.

With its wide opening jaw it replaces two wrenches (6“-8“ for reference 017030, 8“-10“ for reference 017031, etc.)

Triple coating of nickel and chrome provides **high corrosion resistance**.

Ergonomic handle with **anti-slip coating** for better grip.

Fixed jaw graded in mm and inch for adjustment before use.

Complies with ISO 6787:2001 and ASME B107.100-2010 standards.

References

Sku	Accross flats A mm	Accross flats A"	E mm	E1 mm	L mm	L "	kg
017030	27	1.1/16"	5,3	10,8	162	6	0,160
017031	34	1.5/16"	7,2	14,0	209	8	0,320
017032	40	1.9/16"	7,7	15,5	261	10	0,510

Sku	Accross flats A mm	Accross flats A"	E mm	E1 mm	L mm	L "	kg
017033	45	1.3/4"	9,5	19,0	313	12	0,835
017039	27 - 34 - 40	1.1/16" - 1.5/16" - 1.9/16"	5,3 - 7,2 - 7,7	10,8 - 14,0 - 15,5	162 - 209 - 261	6 - 8 - 10	0,990