



Part Number : [1301470175](#)

Product Description : Watertite Extreme Receptacle with Locking Blade, Single Flip Coverplate, 3 Pole/4 Wire, NEMA L16-30, 3ø 480V

Series Number : 130147

Status : Active

Product Category : Wiring Devices

Engineering Number : 69W76



Documents & Resources

Drawings

[1301470175 sd.pdf](#)

3D Models and Design Files

[STEP AP242](#)

[SOLIDWORKS](#)

[Creo](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Reviewed per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D

- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Wiring Devices
Series	130147
Description	Watertite Extreme Receptacle with Locking Blade, Single Flip Coverplate, 3 Pole/4 Wire, NEMA L16-30, 3Ø 480V
IP Rating	IP67
NEMA Configuration	NEMA L16-30
Product Name	Watertite Extreme
Specialty	N/A
Type	Receptacle
UPC	78678871579

Agency

UL	E68122
----	--------

Electrical

Current - Maximum per Contact	30.0A
GFCI	No
Voltage - Maximum	3Ø 480V

Physical

Cord Type	N/A
Flange	No
Flip Lid	Yes

Gender	Female
Length	N/A
Lighted Connector	No
Locking Blade	Yes
Net Weight	32782.448/g
Poles	3-pole/4-wire
Receptacle Type	Single

This document was generated on Nov 05, 2025