

FEATURES

- Vertically Mounted PDU
- Type G – British 3 pin plug
- 12x IEC C13 sockets
- 3 m cable (BS6500)
- Unit switch with neon indicator
- Complies with EN 60950

RS PRO 3m 12 Socket IEC C13 Extension Lead, 230 V

RS Stock No.: 811-7055



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

From RS PRO, this multi-gang power bar is ideal for powering multiple devices from a single electrical mains point. The 13A fused Type G - British 3-pin plug is attached to a lengthy 3 m cable, allowing you to access power where you need it most.

The PDU features a neon indicated protected power switch, for more convenient device management. The power bar features built-in strain relief to prevent wear and tear damage where the cable connects to the socket and plug.

This extension power distribution unit can be vertically rack-mounted, and is perfect for powering multiple rack mounting devices.

General Specifications

Type	Socket Strip
Colour	Black
Number of Sockets	12
Switchable	Yes
Application	Servers, Light and sound, Professional AV studio

Electrical Specifications

Mains Plug Type	Type G - British BS1363
Socket Type	IEC C13
Voltage Rating	230V
Current Rating (Unwound)	13A
Frequency	50/60 Hz

Mechanical Specifications

Mounting type	GE Vertical Mounting Bracket
Cable Length	3m
Cross Sectional Area	1.5 mm ²
Dimensions	600mm x 51mm x 51mm
Height	600mm
Width	51mm
Depth	51mm

Approvals

Compliance/Certifications	EN60950
Standards Met	CE, RoHS



