

FEATURES

- Contact rating 10A 125V-250V ac
- Black steel housing with non-skid base pad - to keep in place when using the footswitch
- Degree of protection - IP20 rated
- Compact and light weight
- Stock number 116-861 is supplied with 6ft cable

RS PRO Light Duty Momentary Foot Switch - Steel Case Material, SP-CO, 10 A @ 250 V ac Contact Current, 250V Contact

RS Stock No.: 116-877



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description ATTRIBUTE 1

RS PRO momentary light duty foot switches which have been designed with an integral non-slip base pad and are manufactured from steel. These foot controller pedals are sealed to IP20.

General Specifications

Contact Configuration	SP-CO
Switch Operation	Momentary
Case Material	Steel
Switch Environment	Light Duty
Colour	Black
Applications	Foot switches are commonly used in applications where hands-free control is more practical or safer. They can be found on: Industrial machinery and smaller power tools, Hospital beds, Dentist Chairs, Lamps
Cable Connection	Provided with an adjustable strain relief clamp that accommodates a wide variety of cable sizes

Electrical Specifications

Contact Voltage Rating (AC)	250V
Contact Current Rating	10A @ 250V ac

Mechanical Specifications

Length	73.02mm
Height	32.54mm
Dimensions	73.02mm x 63.54 x 32.54mm
Width	63.54mm
Weight	0.2kg

Protection Category

IP Rating	IP20
-----------	------

Approvals

Standards Met	EN 60529
Compliance/Certifications	RoHS, CE



Size

(See below)

